

3 ft Cat 6 Yellow Molded Gigabit Crossover RJ45 UTP Cat6 Patch Cable

Product ID: C6CROSS3YL



StarTech.com's Cat 6 UTP Crossover Patch Cables offer reliable Ethernet connections. This 3ft cable is ETL verified to meet or exceed all Category 6 performance standards, and features a durable yellow jacket that simplifies departmental color coding while providing rugged flexibility for network connections.

Featuring top quality construction (100% copper conductors, 23 Gauge Wire and 50 Micron gold connectors), our Cat6 Crossover cables are built to last and backed by lifetime warranty.

Certifications, Reports and Compatibility

Applications

- Use crossover cable to directly connect two computers without the need for a hub
- Connect two Ethernet hubs/switches together with crossover cable
- Category 6 cables support gigabit networks

Features

- StarTech.com Category 6 crossover cables are manufactured to meet or exceed CAT6 specifications
- Molded strain relief and stranded wires for added flexibility and durability
- Colored Hoods for departmental color coding and easy identification
- Molded ends with top-quality connectors

Hardware

Warranty	Lifetime
Number of Conductors	4 pair UTP
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CMG Rated (General Purpose)
Cable Type	Crossover Molded
Wiring Standard	TIA/EIA-568-B.1-2001 T568B

Performance

Cable Rating	CAT6 - 500 MHz
--------------	----------------

Connector(s)

Connector A	RJ-45
Connector B	RJ-45

Physical Characteristics

Color	Yellow
Wire Gauge	24 AWG
Cable Length	36.0 in [91.4 cm]
Product Length	36.0 in [91.4 cm]

Packaging Information

Package Length	7.8 in [19.9 cm]
Package Width	0.5 in [12 mm]
Package Height	8.3 in [21.1 cm]
Shipping (Package) Weight	1.8 oz [50 g]

What's in the Box

Included in Package	3 ft. Yellow Category 6 Crossover Cable
---------------------	---



****Product appearance and specifications are subject to change without notice.***

