

7 ft Cat 6 Yellow Molded Gigabit Crossover RJ45 UTP Cat6 Patch Cable

Productcode: C6CROSS7YL



StarTech.com's Cat 6 UTP Crossover Patch Cables offer reliable Ethernet connections. This 7ft cable is ETL verified to meet or exceed all Category 6 performance standards, and features a durable yellow jacket that simplifies departmental color coding while providing rugged flexibility for network connections.

Featuring top quality construction (100% copper conductors, 23 Gauge Wire and 50 Micron gold connectors), our Cat6 Crossover cables are built to last and backed by lifetime warranty.

Certificaties, rapporten en compatibiliteit

Toepassingen

- Use crossover cable to directly connect two computers without the need for a hub
- Connect two Ethernet hubs/switches together with crossover cable
- Category 6 cables support gigabit networks

Eigenschappen

- StarTech.com Category 6 crossover cables are manufactured to meet or exceed CAT6 specifications
- Molded strain relief and stranded wires for added flexibility and durability
- Colored Hoods for departmental color coding and easy identification

- Molded ends with top-quality connectors

Hardware

Garantiebeleid	Lifetime
Aantal geleiders	4 pair UTP
Type kabelmantel	PVC - Polyvinyl Chloride
Brandbestendigheid	CMG goedgekeurd (algemeen doel)
Type kabel	Crossover Gegoten
Kabelstandaard	TIA/EIA-568-B.1-2001 T568B

Prestaties

Kabelspecificatie	CAT6 - 500 MHz
-------------------	----------------

Connector(en)

Connector A	RJ-45
Connector B	RJ-45

Fysieke eigenschappen

Kleur	Geel
Draaddikte	24 AWG
Type geleider	Gevlochten koper
Kabellengte	7.0 ft [2.1 m]
Lengte product	7.0 ft [2.1 m]

Verpakkingsinformatie

Package Length	7.8 in [19.8 cm]
Package Width	0.6 in [16 mm]
Package Height	8.3 in [21 cm]
Verzendgewicht	3.5 oz [100 g]



(verpakt)

Wat wordt er
meegeleverd

Meegeleverd

7 ft. Yellow Category 6 Crossover Cable

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.

