
Cat6 Keystone Jack, 24-Pack RJ45 Ethernet Keystone Jacks, UTP Cat6 Wall Jack, 90-Degree 110 Punch Down, Blue

Product ID: C6KEY110BL24PK



Terminate in-wall Cat6/Cat5e cable runs using this 24-pack of RJ45 Keystone Jacks. Ideal for structured cabling installations, network expansion, or office reconfigurations, this Cat6 Keystone Jack multipack is a practical solution for terminating multiple drops across wall plates, surface mount boxes, or keystone patch panels.

The Cat6 Keystone Jack features a 90-degree 110 punch down design that positions the cable perpendicular to the jack face. This enables the in-wall cable drop to be terminated in its vertical orientation, eliminating bending strain and preventing long-term cable fatigue. It is suitable for wall plate installations where space behind the plate is limited.

Maintain consistent signal transmission with gold-plated phosphor bronze RJ45 contacts that resist corrosion and help prevent degradation of network performance over time. The Cat6 keystone jack maintains reliable contact pressure to reduce signal loss in high-uptime or critical networks, ensuring long-term reliability in demanding environments.

Plan and execute multi-room cabling projects with consistent hardware at every drop point. The 24-pack format enables standardized terminations across floors, rooms, and offices, eliminating variability from mixed stock and ensuring consistency across larger LAN deployments.

Certifications, Reports and Compatibility

Applications

Features

• Terminate LAN Cable Runs: Use this 24-pack of Cat6/5e RJ45 UTP keystone jacks to support network cable terminations across LAN infrastructure; This multipack is ideal for in-wall cable drops to wall plates or surface mount boxes in meeting rooms and offices

• Align with In-Wall Cabling: Position the 90-degree punch down to match vertical cable drops and terminate into the Cat6 keystone jack without bending; Optimized for in-wall cabling where clearance is limited and straight-through jacks do not fit

• Match Wiring Standards: Use standard 110 punch down tools to terminate RJ45 wiring in T568A or T568B configurations; Wiring schemes are printed on the jack for quick reference; Tool-based terminations provide secure mechanical retention over time

• Standardize Network Compatibility: Enable 10Gbps Ethernet and up to 100W PoE (IEEE 802.3bt Type 4) over Cat6 UTP; Gold-plated contacts enhance conductivity and meets ANSI/TIA-568-C.2 standards; Backward compatible with Cat5e in mixed-cable environments

• The IT Pro's Choice: Our network jacks, connectors, and couplers are tested for peak performance in structured cabling environments; Designed for reliability with consistent fit and finish; Backed by free lifetime 24/5 multi-lingual technical assistance

General		
	UPC	065030912808
	Package Quantity	24
	Warranty	2 Years
Power		
	Power Delivery	100W
Physical & Environmental		
	Color	Blue
	Material	ABS
		Polycarbonate
	Product Length	1.2 in [31.5 mm]
	Product Width	0.7 in [16.6 mm]
	Product Height	0.8 in [19.3 mm]
	Weight of Product	0.2 oz [7 g]
	Operating Temperature	-10&degC to 60&degC (14&degF to 140&degF)

	Storage Temperature	-40&degC to 70&degC (-40&degF to 158&degF)
	Humidity	85%
Hardware		
	Connector Plating	Gold
	Wiring Standard	TIA/EIA-T568A
		TIA/EIA-T568B
	Industry Standards	IEEE 802.3 10/100/1000BASE-T
		IEEE 802.3bz 2.5GBASE-T
		IEEE 802.3bz 5GBASE-T
		IEEE 802.3ae 10GBASE-T
		IEEE 802.3bt Type 4 (4PPoE)
Packaging & In-the-Box		
	Included in Package	24 - Cat 6 Keystone Jack
		24 - Wire Cap
		24 - Dust Cover
		1 - Quick-Start Guide
	Package Width	6.2 in [15.7 cm]
	Package Depth	6.5 in [16.5 cm]
	Package Height	1.7 in [44 mm]
	Shipping (Package) Weight	7.2 oz [203 g]

Product appearance and specifications are subject to change without notice.