

180° Cat 6 Keystone Jack - RJ45 Ethernet Cat6 Wall Jack White - 110 Type

Produkt ID: C6KEY110SWH



The C6KEY110SWH Cat6 Keystone Jack is designed to snap into wall plates, patch panels, and surface connection boxes for quick, seamless deployment.

Meeting and exceeding the international standard ISO / IEC 11801 and the ANSI/TIA-568-C.2 requirements, this RJ45 keystone jack provides the perfect solution for your Ethernet networks.

Durably constructed of only top quality materials, this Cat6 wall jack is backed by StarTech.com's 2 year warranty.

Certifikat, rapporter och kompatibilitet



Användning

- Suitable for applications that use 23-26 AWG solid state and stranded network cables
- 1000BASE-T Gigabit Ethernet, 100BASE-TX Fast Ethernet, 10BASE-T Ethernet applications
- ATM-25/ATM-51/ATM-155 network connections
- 100 VG-AnyLan network connections
- TR-4/TR-16 Active/TR16 Passive network connections

Funktioner

- The wall jack features a high-impact, flame retardant (UL 94V0) plastic housing
- Meets and exceeds the international standard ISO / IEC 11801 and the ANSI/TIA-568-C.2 requirements
- Dual-type IDC connectors, situated 180° relative to the RJ45 ports, terminated using 110-type punch tool
- Color coded for both T568A and T568B installations

Kontakt(er)

Garantipolicy	2 Years
Kontakttyp(er)	1 - RJ-45

Utseende

Färg	Vit
Produktlängd	1.4 in [35 mm]
Produktbredd	0.7 in [1.7 cm]
Produkthöjd	0.9 in [2.2 cm]
Produktvikt	0.2 oz [7 g]

Förpackning

Förpackningsantal	1
Paketets längd	4.9 in [12.5 cm]
Paketets bredd	3.5 in [9.0 cm]
Paketets höjd	0.6 in [1.4 cm]
Fraktvikt (förpackning)	0.3 oz [9.0 g]

Vad det är i lådan

Ingår i paketet	1 - 180° Cat 6 RJ45 Keystone Jack White - 110 Type
-----------------	--

Warranty

Information

Warranty

2 År

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.