

## 24 Port 1U Blank Keystone Patch Panel, Rackmount Cat6 Patch Panel for RJ45 UTP Ethernet Network Jacks

**Product ID:** C6PANELUTP241U



Deploy multiple Ethernet cable terminations in rack-mounted network setups, using this 24-Port 1U Blank Keystone Patch Panel. It is designed for high-density installations such as wiring closets and data centers, where modular port configuration is key to long-term serviceability.

The 1U keystone patch panel supports unshielded (UTP) RJ45 keystone jacks for fast, tool-free setup and configuration. Numbered port labels on the front panel provide easy identification during troubleshooting and routine maintenance.

The steel housing features a black powder-coated finish for scratch resistance and long-term durability. The included grounding wire supports proper termination for shielded installations.

### Certifications, Reports and Compatibility



### Applications

- For installation in standard 19in network racks and cabinets
- Enable instant Cat6 connectivity with RJ45 keystone jacks. Quickly swap jacks as needed for configuration and troubleshooting
- Clearly numbered keystone ports make it easy to identify your cable runs

## Features

- **Customize Patch Panel Layout**: Install up to 24 UTP RJ45 keystone jacks for high-performance networking; 1U blank keystone panel features a toolless, modular design with clearly numbered ports; Ideal for modular and scalable network builds
- **Identify Ports Quickly**: Front-facing numbered ports provide clear labeling for instant cable identification; Simplify maintenance and reduce errors during network changes or expansions
- **Streamline Network Terminations**: Install Cat5e or Cat6 UTP keystone jacks without punch down tools; Quickly replace jacks as needed to maintain service continuity and minimize downtime
- **Mount in Any Standard Rack**: Includes mounting screws and cage nuts for installation into any 19in rack or wall-mount enclosure; Toolless keystone slots support fast, flexible deployment during upgrades or rollouts
- **The IT Pro's Choice**: Designed for reliability in edge and on-prem deployments, our networking solutions are lab-tested and field-proven for seamless integration and maximum uptime; Backed by free lifetime 24/5 multi-lingual technical assistance

---

### Environmental

Warranty	3 Years
Operating Temperature	-10&degC to 60&degC (14&degF to 140&degF)
Storage Temperature	-40&degC to 70&degC (-40&degF to 158&degF)
Humidity	85%

---

### Physical Characteristics

Color	Black
Material	Steel
Product Length	19.0 in [482.6 mm]
Product Width	0.6 in [14.9 mm]
Product Height	1.7 in [44.4 mm]
Weight of Product	11.8 oz [334 g]

---

### Packaging Information

Package Length	2.4 in [6.0 cm]
Package Width	20.1 in [51.0 cm]
Package Height	2.4 in [6.0 cm]

Shipping (Package) Weight	15.8 oz [448.0 g]
------------------------------	-------------------

---

**What's in the Box**

Included in Package	1 - Patch Panel
	1 - Product Documentation
	1 - Set of Screws and Nuts

---

**Warranty  
Information**

Warranty	3 Years
----------	---------

---

***\*Product appearance and specifications are subject to change without notice.***