

24 Port 1U Feed Through Patch Panel with Cable Management Bar, Rackmount Cat6 Ethernet Patch Panel with RJ45 UTP Inline Couplers

Product ID: C6PANELUTP241UFT



Streamline rack-mounted network setups with this 24-Port 1U Feed-Through Patch Panel with preinstalled RJ45 UTP inline couplers. Designed for scalable enterprise networks, it provides a clean, ready-to-use solution for organizing Cat6 or Cat5e patch cables across standard 19-inch racks.

Each port includes a factory-installed RJ45 coupler that supports Cat6 and Cat5e Ethernet cabling, with clearly numbered ports on the front panel to simplify identification, maintenance, and network reconfiguration. Instantly swap or replace patch cables as needed to restore connections quickly and minimize downtime.

The steel housing features a black powder-coated finish for scratch resistance and long-term durability. An integrated cable management bar with tie-down slots reduces cable strain and maintains a tidy setup, improving passive airflow and ease of access when troubleshooting.

Certifications, Reports and Compatibility



Applications

- For installation in standard 19in network racks and cabinets
- Connect Cat6/5e cables instantly without punch down tools. Quickly swap cables as needed for configuration and troubleshooting
- Clearly numbered keystone ports make it easy to identify your cable runs

Features

- **Toolless Feed-Through Layout:** Simplify network setups with a ready-to-use 24-port 1U feed-through patch panel; Pre-installed RJ45 UTP couplers deliver instant Cat6/5e connectivity with no punch-downs or crimping; Designed for efficient, scalable installations
- **Route Cables Cleanly:** Neatly organize cabling with the rear cable management bar, featuring individual U-shaped cable guides and side anchor slots for attaching cable ties; Maintain a tidy rack layout for improved airflow, easy access and troubleshooting
- **Streamline Network Connections:** Eliminate manual terminations by connecting Cat6 patch cords directly on both sides with RJ45 inline couplers; Quickly replace cables as needed to maintain service continuity and minimize downtime
- **Mount in Any Standard Rack:** Includes mounting screws and cage nuts for installation into any 19in rack or wall-mount enclosure; Toolless keystone slots support fast, flexible deployment during upgrades or rollouts
- **The IT Pro's Choice:** Designed for reliability in edge and on-prem deployments, our networking solutions are lab-tested and field-proven for seamless integration and maximum uptime; Backed by free lifetime 24/5 multi-lingual technical assistance

General

UPC	065030911924
Warranty	3 Years

Physical & Environmental

Color	Black
Material	Steel
Product Length	19.0 in [482.6 mm]
Product Width	5.4 in [138.3 mm]
Product Height	1.7 in [44.3 mm]
Weight of Product	22.2 oz [630 g]
Operating Temperature	-10°C to 60°C (14°F to 140°F)
Storage Temperature	-40°C to 70°C (-40°F to 158°F)
Humidity	85%

Packaging & In-the-Box

Included in Package	1 - Patch Panel
	1 - Product Documentation
	1 - Set of Screws and Nuts
Package Width	2.8 in [70 mm]
Package Depth	20.3 in [515 mm]
Package Height	2.4 in [60 mm]
Shipping (Package) Weight	25.9 oz [733 g]

****Product appearance and specifications are subject to change without notice.***