

24 Port 1U Rackmount Cat 6 110 Patch Panel - 45 Degree

Product ID: C6PANL4524



The C6PANL4524 24 Port 110 type Rack Mount Cat 6 Patch Panel is color coded for both T568A and T568B wiring providing the perfect solution for any voice or LAN application.

The patch panel offers 45 downward tilted ports and 110-type termination. Plus, the port numbers are clearly marked on the back of each RJ45 port, offering a quick and easy way to identify cable runs.

Durably constructed of only top quality materials, this 24-port Ethernet patch panel is backed by StarTech.com's 2 year warranty.

Certifications, Reports and Compatibility

Applications

- For installation in 19" rack/cabinets
- Suitable for applications that use 22-26 AWG solid state and standard network cables
- 1000BASE-T Gigabit Ethernet, 100BASE-TX Fast Ethernet, 10BASE-T Ethernet applications
- Voice, video and other applications

Features

- Color coded for both T568A and T568B installations
- Terminated using 110-type punch tool

- Supports both Cat5e and Cat6 cables

Physical Characteristics

Warranty	2 Years
Product Length	19.0 in [48.3 cm]
Product Width	2.2 in [57.2 mm]
Product Height	1.7 in [44.4 mm]
Weight of Product	18.1 oz [512.0 g]

Packaging Information

Package Length	22.0 in [56.0 cm]
Package Width	4.0 in [10.2 cm]
Package Height	3.0 in [76.0 mm]
Shipping (Package) Weight	23.9 oz [676.0 g]

What's in the Box

Included in Package	Patch Panel
	Rackmount
	Instruction manual

**Product appearance and specifications are subject to change without notice.*

