15m Cat 6 Black Molded RJ45 UTP Gigabit Cat6 Patch Cable - 15 m Patch Cord

Produkt ID: C6PAT15MBK

The C6PAT15MBK Cat 6 Patch Cable (15m) meets or exceeds all Category 6 cable specifications to ensure reliable Gigabit network connections, and features a durable black PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat 6 patch cable features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Gigabit Patch Cable delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat6 cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat6 cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This molded patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Certifikat, rapporter och kompatibilitet

Användning

• Framtagen för att användas med gigabit-nätverk

• Kopplar från hubb till distributionspanel

• Anslut en arbetsstation till ett vägguttag

• Förläng ditt Gigabit-nätverks täckning med 15 m

Funktioner

• Gjutna RJ45-kontakter

• Tillverkad och testad med omsorg för att bakåtöverhörning (NEXT) ska ligga väl inom godkända gränser

• Färgade huvor så att man kan färgkoda olika avdelningar

• Tillverkad av komponenter med toppkvalitet

• Högkvalitativ 0,25 mm² koppartråd

• ETL-godkänd

Hårdvara		
	Garantipolicy	Lifetime
	Antal ledare	4 Pair UTP
	Kabelmanteltyp	PVC - Polyvinyl Chloride
	Brandteknisk klass	CMG-klass (General Purpose)
	Kabeltyp	Gjuten
	Kabelstandard	TIA/EIA-568-B.1-2001 T568B
Prestanda		
	Kabelklassificering	CAT6 - 650 MHz

Kontakt(er)		
	Connector A	1 - RJ-45
	Connector B	1 - RJ-45
Utseende		
	Färg	Svart
	Tråddimension	24 AWG
	Ledningstyp	Tvinnad koppar
	Kabellängd	49.2 ft [15 m]
	Produktlängd	49.2 ft [15 m]
	Produktvikt	20.4 oz [579 g]
Förpackning		
	Förpackningsantal	1
	Package Length	13.0 in [33 cm]
	Package Width	9.8 in [25 cm]
	Package Height	1.6 in [40 mm]
	Fraktvikt (förpackning)	1.3 lb [0.6 kg]
Vad det är i lådan		
	Ingår i paketet	1 - 15m Black Molded Cat6 UTP Patch Cable - ETL Verified

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.