

Cat6 Patch Cable with Molded RJ45 Connectors - 15 m - Gray

Produkt ID: C6PAT15MGR



The C6PAT15MGR Cat 6 Patch Cable (15m) meets or exceeds all Category 6 cable specifications to ensure reliable Gigabit network connections, and features a durable gray PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat 6 patch cable features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Gigabit Patch Cable delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat6 cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat6 cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This molded patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Certifikat, rapporter och kompatibilitet



Användning

- Framtagen för att användas med gigabit-nätverk
- Kopplar från hubb till distributionspanel
- Anslut en arbetsstation till ett vägguttag
- Förläng ditt Gigabit-nätverks täckning med 15 m

Funktioner

- Gjutna RJ45-kontakter
- Tillverkad och testad med omsorg för att bakåtoverhörning (NEXT) ska ligga väl inom godkända gränser
- Färgade huvor så att man kan färgkoda olika avdelningar
- Tillverkad av komponenter med toppkvalitet
- Högkvalitativ 0,25 mm² koppartråd
- ETL-godkänd

Hårdvara

Garantipolicy	Lifetime
Antal ledare	4 Pair UTP
Kabelmanteltyp	PVC - Polyvinyl Chloride
Brandteknisk klass	CMG-klass (General Purpose)
Kabeltyp	Gjuten
Kabelstandard	TIA/EIA-568-B.1-2001 T568B

Prestanda

Kabelklassificering	CAT6 - 650 MHz
---------------------	----------------

Kontakt(er)	Connector A	1 - RJ-45
	Connector B	1 - RJ-45
Utseende		
	Färg	Grå
	Tråddimension	24 AWG
	Ledningstyp	Tvinnad koppar
	Kabellängd	49.2 ft [15 m]
	Produktlängd	49.2 ft [15 m]
	Produktbredd	0.0 in [0.0 cm]
	Produkthöjd	0.0 in [0.0 cm]
	Produktvikt	1.3 lb [0.6 kg]
Förpackning		
	Förpackningsantal	1
	Paketets längd	13.0 in [33.0 cm]
	Paketets bredd	10.0 in [25.5 cm]
	Paketets höjd	1.7 in [4.2 cm]
	Fraktvikt (förpackning)	1.3 lb [0.6 kg]
Vad det är i lådan		
	Ingår i paketet	1 - 15 m Cat6 Patch Cable - Gray
Warranty Information		
	Warranty	Livslängd

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.