

Cat6 Patch Cable with Molded RJ45 Connectors - 15 m - Gray

Product ID: C6PAT15MGR



The C6PAT15MGR Cat 6 Patch Cable (15m) meets or exceeds all Category 6 cable specifications to ensure reliable Gigabit network connections, and features a durable gray PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat 6 patch cable features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Gigabit Patch Cable delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat6 cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat6 cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This molded patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Certifications, Reports and Compatibility

Applications

- Connects workstation to wall outlet

- Patches from hub to distribution panel
- Designed for use with Gigabit networks
- Extend the reach of your Gigabit network devices by 15m (49.2ft)

Features

- Constructed with top quality components
- High quality 24 AWG copper wire
- Colored hoods for departmental color coding
- Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits
- Molded RJ45 connectors
- ETL Verified

Hardware

Warranty	Lifetime
Number of Conductors	4 Pair UTP
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CMG Rated (General Purpose)
Cable Type	Molded
Wiring Standard	TIA/EIA-568-B.1-2001 T568B

Performance

Cable Rating	CAT6 - 650 MHz
--------------	----------------

Connector(s)

Connector A	RJ-45
Connector B	RJ-45

Physical Characteristics

Color	Gray
Wire Gauge	24 AWG



Conductor Type	Stranded Copper
Cable Length	49.2 ft [15 m]
Product Length	49.2 ft [15 m]
Product Width	0.0 in [0 mm]
Product Height	0.0 in [0 mm]
Weight of Product	20.3 oz [576 g]

Packaging Information

Package Quantity	1
Package Length	13.0 in [33 cm]
Package Width	10.0 in [25.5 cm]
Package Height	1.7 in [42 mm]
Shipping (Package) Weight	21.0 oz [595 g]

What's in the Box

Included in Package	15 m Cat6 Patch Cable - Gray
---------------------	------------------------------

**Product appearance and specifications are subject to change without notice.*

