

91cm CAT6 Patchkabel - 10 Pack - 100% Kupferdraht - Blue

Produkt-ID: C6PATCH3BL10PK



This CAT6 cable pack meets all Category 6 cable specifications, to deliver a reliable Gigabit network connection.

The CAT6 patch cable 10-pack is built using 100% copper wire and are tested to comply with ANSI/TIA 568 C.2 Category 6 requirements. We don't use copper-clad aluminum (CCA) wire, which is subject to problems like weak power delivery, heat buildup, equipment damage and possibly fire.

The 50-micron gold connectors deliver optimum conductivity and eliminate signal loss due to oxidation or corrosion.

The CAT6 Ethernet cords are manufactured using high-quality copper conductors and carefully constructed and tested to keep Near-End Crosstalk (NEXT) well within acceptable limits. The patch cables are built with 24 AWG copper wire, to ensure peak performance for demanding Ethernet applications such as Power-over-Ethernet and 4K or 1080p video streaming.

For trouble-free cable runs, these durable cables feature molded boots which offer strain relief by stopping the RJ45 connectors from bending at sharp angles. This reduces the risk of cable damage, which could decrease network connectivity and performance.

Our Bulk Cat5e cables are ETL Verified to meet ANSI/TIA-568.2-D standards, ensuring peak performance for high-speed applications. Independent testing confirms compliance with strict insertion loss, return loss, and crosstalk limits, maintaining stable signal transmission over longer runs.

C6PATCH3BL10PK is backed by a StarTech.com lifetime warranty for guaranteed reliability.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Designed for use with Gigabit networks
- Patches from hub to distribution panel
- Connects workstation to wall outlet

Merkmale

- 100% COPPER WIRING: Each CAT6 Ethernet cable is built with 100% copper wiring to prevent weak power delivery and equipment damage, compared to copper-clad aluminum wire cables; ETL Verified to meet ANSI/TIA-568.2-D standards
- ETL VERIFIED: This CAT6 cable 10 pack is ETL Verified to ensure an elevated level of quality and reliability. Each CAT6 patch cord is tested to comply with ANSI/TIA-568-D Category 6 requirements
- CABLE PERFORMANCE: Length: 3 ft. (1 m) Color: Blue | Cable Structure: 4 Pair UTP | Connector Type: Molded | Jacket Material: PVC | Wire Gauge: 24 AWG | Wiring Standard: ANSI/T568B
- EASY INSTALLATION: Blue molded patch cord is easy to connect into high density panels with many cables; Compatible w/Cat5e; Available w/Snagless boots for easy wiring conduit installation
- CAT6 PATCH CABLE MULTIPACK: This 10 pack of 3 ft. Blue patch cords is a convenient and affordable option for businesses in need of multiple molded ethernet cables

Hardware

Garantiebestimmungen Lifetime

Anzahl von Leitern 4 Pair UTP

Typ der PVC - Polyvinyl Chloride
Kabelummantelung

Feuerwiderstandsklass Ausgelegt gemäß CMG (Mehrzweck)
e

Kabeltyp Vergossen

Verkabelungsstandard TIA/EIA-568-B.1-2001 T568B

Leistung

ETL-verifiziert	Ja
Kabelnennwerte	CAT6 - 250 MHz

Steckverbinder

Steckverbinder A	1 - RJ-45
Steckverbinder B	1 - RJ-45

Physische
Eigenschaften

Farbe	Blau
Drahtstärke	24 AWG
Leitungstyp	Feindrähtiges Kupfer
Kabellänge	3.0 ft [0.9 m]
Produktlänge	36.0 in [91.4 cm]
Produktbreite	0.5 in [1.2 cm]
Produkthöhe	0.3 in [0.8 cm]
Produktgewicht	15.9 oz [450 g]

Verpackungsinfo-
rmati-
onen

Paketmenge	10
Paketlänge	12.2 in [31.0 cm]
Paketbreite	9.8 in [24.8 cm]
Pakethöhe	2.4 in [6.1 cm]
Versandgewicht (Verpackung)	1.0 lb [0.5 kg]

Verpackungsinhalt

Im Paket enthalten	10 - CAT6-Kabel
--------------------	-----------------

Garantieinformatio-
nen

Warranty

Lifetime

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.

