

1,8m CAT6 Patchkabel - 10 Pack - 100% Kupferdraht - Blue

Produkt-ID: C6PATCH6BL10PK



This CAT6 cable pack meets all Category 6 cable specifications, to deliver a reliable Gigabit network connection.

The CAT6 patch cable 10-pack is built using 100% copper wire and are tested to comply with ANSI/TIA 568 C.2 Category 6 requirements. We don't use copper-clad aluminum (CCA) wire, which is subject to problems like weak power delivery, heat buildup, equipment damage and possibly fire.

The 50-micron gold connectors deliver optimum conductivity and eliminate signal loss due to oxidation or corrosion.

The CAT6 Ethernet cords are manufactured using high-quality copper conductors and carefully constructed and tested to keep Near-End Crosstalk (NEXT) well within acceptable limits. The patch cables are built with 24 AWG copper wire, to ensure peak performance for demanding Ethernet applications such as Power-over-Ethernet and 4K or 1080p video streaming.

For trouble-free cable runs, these durable cables feature molded boots which offer strain relief by stopping the RJ45 connectors from bending at sharp angles. This reduces the risk of cable damage, which could decrease network connectivity and performance.

Our Bulk Cat5e cables are ETL Verified to meet ANSI/TIA-568.2-D standards, ensuring peak performance for high-speed applications. Independent testing confirms compliance with strict insertion loss, return loss, and crosstalk limits, maintaining stable signal transmission over longer runs.

C6PATCH6BL10PK is backed by a StarTech.com lifetime warranty for guaranteed reliability.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Designed for use with Gigabit networks
- Patches from hub to distribution panel
- Connects workstation to wall outlet

Merkmale

- **100% COPPER WIRING:** Each CAT6 Ethernet cable is built with 100% copper wiring to prevent weak power delivery and equipment damage, compared to copper-clad aluminum wire cables; ETL Verified to meet ANSI/TIA-568.2-D standards
- **ETL VERIFIED:** This CAT6 cable 10 pack is ETL Verified to ensure an elevated level of quality and reliability. Each CAT6 patch cord is tested to comply with ANSI/TIA-568-D Category 6 requirements
- **CABLE PERFORMANCE:** Length: 6 ft. (1.8 m) Color: Black | Cable Structure: 4 Pair UTP | Connector Type: Molded | Jacket Material: PVC | Wire Gauge: 24 AWG | Wiring Standard: ANSI/T568B
- **EASY INSTALLATION:** Black molded patch cord is easy to connect into high density panels with many cables; Compatible w/Cat5e; Available with molded boots for easy wiring conduit installation
- **CAT6 PATCH CABLE MULTIPACK:** This 10 pack of 6 ft. Black patch cords is a convenient and affordable option for businesses in need of multiple molded ethernet cables

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	4 Pair UTP
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Feuerwiderstandssklasse	Ausgelegt gemäß CMG (Mehrzweck)e
Kabeltyp	Vergossen
Verkabelungsstandard	TIA/EIA-568-B.1-2001 T568B

Leistung	ETL-verifiziert	Ja
	Kabelnennwerte	CAT6 - 250 MHz
Steckverbinder	Steckverbinder A	1 - RJ-45
	Steckverbinder B	1 - RJ-45
Physische Eigenschaften	Farbe	Blau
	Drahtstärke	24 AWG
	Leitungstyp	Feindrähtiges Kupfer
	Kabellänge	6.0 ft [1.8 m]
	Produktlänge	72.3 in [1837.0 mm]
	Produktbreite	0.5 in [1.2 cm]
	Produkthöhe	0.5 in [1.2 cm]
	Produktgewicht	2.8 oz [80.0 g]
Verpackungsinformationen	Paketmenge	10
	Paketlänge	8.5 in [21.7 cm]
	Paketbreite	8.6 in [21.9 cm]
	Pakethöhe	2.7 in [6.8 cm]
	Versandgewicht (Verpackung)	1.9 lb [0.8 kg]
Verpackungsinhalt		
	Im Paket enthalten	10 - CAT6-Kabel
Garantieinformationen		

Warranty

Lifetime

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.