Cat8 Keystone Jack, 6-Pack RJ45 Ethernet Keystone Jacks, STP Cat8 Wall Jack, 180-Degree Toolless

Product ID: C8KEYSTP1806PK



Use this 6-pack of Toolless Cat8 RJ45 Keystone Jacks to terminate Cat8 network links quickly and cleanly without punch down tools. Designed for enterprise 25G/40G networks and infrastructure, this Cat8 keystone jack set offers a reliable solution for terminating shielded cables to high-speed patch panels.

The Toolless Cat8 Keystone Jack features a 180-degree layout that supports straight cable entry from the rear, suitable for keystone patch panels and wall plates with open clearance. This layout enables clean, straight-through terminations without re-positioning the cable.

Maintain signal integrity in high-density installations with a zinc alloy housing and nickel-plated shielding designed to minimize EMI. Gold-plated phosphor bronze RJ45 contacts ensure stable connectivity, for long-term reliability in high-uptime networks and demanding environments.

Plan and execute multi-room cabling projects with consistent hardware at every drop point. The 6-pack format enables standardized terminations, eliminating variability from mixed stock and ensuring consistency across larger LAN deployments.

Certifications, Reports and Compatibility

Applications

Features

• Terminate Cat8 Cable Runs: Use this 6-pack of Toolless Cat8 RJ45 STP keystone jacks to quickly terminate shielded 25G/40G network cable drops; This multipack is ideal for high-speed patch panels and wall plates across critical LAN infrastructure

• Fit Rackmount Panel Layouts: Toolless Cat8 keystone jack has a 180-degree orientation to support straight rear cable terminations; Ideal for patch panels and wall plates where in-line orientation is preferred and rear clearance is not a constraint

• Simplify Wiring Connections: Terminate RJ45 wiring in T568A or T568B configurations without punch down tools; Wiring schemes are printed on the jack for quick reference; Toolless design enables quick installation and reconfiguration when needed

• Standardize Network Compatibility: Enable 25Gbps/40Gbps Ethernet and up to 100W PoE (IEEE 802.3bt Type 4) over Cat8 STP; Gold-plated contacts enhance conductivity and meets ANSI/TIA-568-C.2 standards; Backward compatible with Cat6/6a in mixed-cable environments

• The IT Pro's Choice: Our network jacks, connectors, and couplers are tested for peak performance in structured cabling environments; Designed for reliability with consistent fit and finish; Backed by free lifetime 24/5 multi-lingual technical assistance

General		
	UPC	065030919807
	Package Quantity	6
	Warranty	Lifetime
Power		
	Power Delivery	100W
Physical & Environmental		
	Color	Silver
	Material	Polycarbonate
		Nickel-plated Zinc
	Product Length	1.1 in [29.2 mm]
	Product Width	0.6 in [16.3 mm]
	Product Height	0.8 in [20.1 mm]
	Weight of Product	0.6 oz [18 g]
	Operating Temperature	-10&degC to 60&degC (14&degF to 140&degF)

	Storage Temperature	-40&degC to 70&degC (-40&degF to 158&degF)
	Humidity	85%
Hardware		
	Connector Plating	Gold
	Wiring Standard	TIA/EIA-T568A
		TIA/EIA-T568B
	Industry Standards	IEEE 802.3 10/100/1000BASE-T
		IEEE 802.3bz 2.5GBASE-T
		IEEE 802.3bz 5GBASE-T
		IEEE 802.3ae 10GBASE-T
		IEEE 802.3ba 40GBASE-T
		IEEE 802.3bq 25GBASE-T
		IEEE 802.3bt Type 4 (4PPoE)
Packaging & In-the-Box		
	Included in Package	6 - Cat 8 Keystone Jack
		6 - Wire Cap
		6 - Dust Cover
		1 - Quick-Start Guide
	Package Width	2.2 in [56 mm]
	Package Depth	4.2 in [10.6 cm]
	Package Height	1.0 in [26 mm]
	Shipping (Package) Weight	4.8 oz [137 g]

Product appearance and specifications are subject to change without notice.