

10U 19in Wall Mounted Server Rack Cabinet

Product ID: CAB1019WALL



The CAB1019WALL 10U Wall Mounted Server Rack Cabinet can be mounted to most wall materials, allowing you to securely position your rackmount equipment exactly as needed. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The server rack offers 10U of storage space and is designed to accommodate standard 19in (wide) rack equipment. To ensure a cool operating environment for your equipment, the server rack includes a 5in roof-mounted fan (85 CFM) and vented side panels - not only helping to keep temperatures down, but keep dust out of the rack.

To secure network and server equipment from tampering, the cabinet features a lockable, smoked acrylic front door, that can be removed entirely or installed to open from the left or right as needed.

Backed by a StarTech.com Lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or superstore location
- Ideal for small and medium businesses requiring small rack solutions dispersed throughout the organization
- Mount Audio/Video broadcast or distribution components

Features

- Front door is removable and can be switched to open left or right

- Includes one, roof-mounted 5" (12cm) fan for up to 85 CFM of airflow
- Ships fully assembled and ready to use
- Includes a lockable & removable smoked acrylic front door with 2 keys
- Stylish enclosure is designed for durability and easy accessibility
- TAA compliant for GSA Schedule purchases

Hardware

Warranty	Lifetime
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Aluminum
U Height	10U
Special Features	Ships Fully Assembled Wall-Mountable
Mounting Rail Profile	L-Shape
Fan Options	One Fan Included: 120 mm + One Optional Fan: 120 mm
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Airflow Rate	82 CFM
Audible Noise	38 dBA @ 1 Meter
Weight Capacity	132.6 lb [60 kg]

Physical Characteristics

Color	Off White
Front Door Construction	Steel with Glass/Acrylic Window
Front Door Features	Secure Key Lock with Reversible and Removable Front Door

Side Panel Construction Steel

Product Measurements

Internal Width	21.9 in [55.5 cm]
Internal Depth	23.4 in [59.5 cm]
Product Length	23.5 in [59.8 cm]
Product Width	22.0 in [56 cm]
Product Height	20.0 in [50.9 cm]
Weight of Product	38.5 lb [17.4 kg]
Maximum Mounting Depth	19.4 in [49.2 cm]

Packaging Information

Flat Pack (Assembly Required)	No
Package Length	25.2 in [64 cm]
Package Width	26.5 in [67.2 cm]
Package Height	25.4 in [64.5 cm]
Shipping (Package) Weight	47.5 lb [21.5 kg]

What's in the Box

Included in Package	10U Server Rack Cabinet
	Instruction Manual
	M5 Screws
	M5 Cage Nuts
	Wall Anchor
	Lag Screws
	Keys



****Product appearance and specifications are subject to change without notice.***

