

Refurbished 10U 19in Wall Mounted Server Rack Cabinet

Product ID: CAB1019WALLR



Refurbished cabinets may have minor scratches and dents similar to photos.

This refurbished 10U Wall Mounted Server Rack Cabinet can be mounted to most wall materials, allowing you to securely position your rackmount equipment exactly as needed.

The server rack offers 10U of storage space and is designed to accommodate 19in (wide) equipment. To ensure a cool operating environment for your networking equipment, the server rack includes a 5in roof-mounted fan (85 CFM) and vented side panels - not only helping to keep temperatures down, but keep dust out of the rack.

To secure network equipment from tampering, the cabinet features a lockable, smoked acrylic front door, that can be removed entirely or installed to open to the left or right as needed.

Units include complete mounting hardware and accessories as intended with the original (non-refurbished) product, and are provided in the original packaging. Refurbished units may have small scratches in the paint on the metal casing, but all other components are as new. Backed by a 90-day replacement warranty,.

Certifications, Reports and Compatibility



Applications

- Mounting standard 19 in. networking equipment in exposed or insecure locations
- Data centers
- Industrial control centers

- Telecommunication closets
- Audio/Visual control centers

Features

- Comes fully assembled
- Front door is removable and can be switched to open left or right
- Fully adjustable mounting rails inside cabinet
- Includes (1) 5" (12cm) Ball bearing AC fan moving up to 85 CFM of air, lockable & removable smoked acrylic front door with 2 keys
- One roof-mounted fan exhaust up to 85 CFM of air
- Stylish enclosure is designed for durability and easy accessibility

Hardware

Warranty	None
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Steel
U Height	10U
Front Door Construction	Steel with Glass/Acrylic Window
Front Door Features	Secure Key Lock
Side Panel Construction	Steel
Fan(s)	Yes
Industry Standards	EIA RS310-C

Performance

Weight Capacity (Stationary)	132.3 lb [60 kg]
Air Flow Rate	85 CFM

Power

Input Voltage	115V AC
---------------	---------

	Input Current	180 mA
<hr/>		
Physical Characteristics		
	Color	Beige
	Internal Width	18.3 in [46.5 cm]
	Internal Depth	22.7 in [57.7 cm]
	Weight of Product	48.5 lb [22.0 kg]
	Maximum Mounting Depth	19.0 in [48.3 cm]
<hr/>		
Packaging Information		
	Flat Pack (Assembly Required)	No
	Package Length	26.2 in [66.5 cm]
	Package Width	27.4 in [69.5 cm]
	Package Height	25.4 in [64.5 cm]
	Shipping (Package) Weight	51.1 lb [23.2 kg]
<hr/>		
What's in the Box		
	Included in Package	1 - Cabinet
		1 - Mounting Bracket
		1 - Set of Keys
		1 - Package of Cab Screw Cage Nut
<hr/>		

****Product appearance and specifications are subject to change without notice.***