

2U 22in Depth Fixed Rack Mount Shelf - 50lbs / 22kg

Product ID: CABSHELF22



The CABSHELF22 2U 22in Depth Fixed Rack Mount Shelf lets you add a compact, 2U shelf to virtually any standard 19-inch server rack or cabinet with front mount options. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Our high-quality rack shelves are designed to withstand harsh work environments with ease. Constructed using SPCC commercial grade cold-rolled steel, this durable fixed rack shelf can hold up to 22kg (50lbs) of equipment - a perfect solution for storing small, non-rackmount equipment, tools, peripherals or accessories in your rack to keep them readily accessible.

Backed by a StarTech.com Lifetime warranty.

Certifications, Reports and Compatibility



Applications

- For use with all 19" wide Server Racks and Cabinets
- Supply additional storage space for mission critical hardware and non-rack mount equipment

Features

- Fits all standard 19" server racks
- SPCC 1.6mm Cold-rolled steel construction
- Front mount design
- Holds up to 22kg (50lbs)
- 2U Fixed Rackmount Shelf

- TAA compliant for GSA Schedule purchases

Hardware	Warranty	Lifetime
	Frame Type	Steel
	U Height	2U
	Cable Management	No
	Mounting Options	Front Mount (Front Only)
Performance	Weight Capacity (Stationary)	50.0 lb [22.6 kg]
Physical Characteristics	Color	Black
	Material	Steel
	Rail Thickness	0.1 in [1.6 mm]
	Product Length	22.0 in [5.6 cm]
	Product Width	18.3 in [4.6 cm]
	Product Height	3.5 in [88.000 mm]
	Weight of Product	8.2 lb [3.7 kg]
Packaging Information	Package Length	23.0 in [5.8 cm]
	Package Width	22.3 in [5.7 cm]
	Package Height	4.3 in [1.1 cm]
	Shipping (Package) Weight	10.7 lb [4.8 kg]
What's in the Box	Included in Package	2U rack shelf
	Included in Package	M5 cage nuts
	Included in Package	M5 screws
	Included in Package	instruction manual

****Product appearance and specifications are subject to change without notice.***

