


1U Vented Server Rack Cabinet Shelf - 10in Deep Fixed Cantilever Tray - Rackmount Shelf for 19" AV/Data/Network Equipment Enclosure with Cage Nuts & Screws - 44lbs capacity

Product ID: CABSHELFV1U



This 1U rack shelf lets you add 10 in. of flat storage space to any EIA-310 compliant server rack or cabinet. The shelf is vented to improve air flow and help lower temperatures in your rack.

The durable fixed-rack shelf can hold up to 20 kg (44 lbs.) of equipment and is constructed using SPCC commercial-grade cold-rolled steel.

The 1U cantilever shelf lets you optimize your working space by giving you the ability to mount equipment to your rack instead of taking up desk or floor space. It's perfect for your SOHO (small office, home office) environment, server room or any other location with limited space available.

You can install the 1U vented rack shelf in your rack at any height, giving you a stable surface for placing equipment that's un-mountable or storing your tools.

The CABSHELFV1U is backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Supply additional storage space for mission-critical hardware and non-rackmount equipment

Features

- **UNIVERSAL COMPATIBILITY:** 1U 19" server rack cabinet shelf 10" deep for universal fit in any existing EIA/ECA-310 compliant server/AV rack or cabinet & includes M6 Cage nuts & screws for mounting shelf

- **VENTED SHELF:** This data/network rack shelf improves airflow around devices on the shelf and within the rack
- **DURABLE DESIGN:** Heavy-duty cantilever shelf tray that is easy to install, constructed of durable 16 gauge SPCC commercial cold-rolled steel with support for weight up to 44 lbs with lifetime warranty
- **FLEXIBLE INSTALLATION:** The rackmount shelf can be mounted in multiple orientations to enable flexibility when it comes to install methods, w/ridge on one side to prevent equipment sliding off
- **LIFETIME WARRANTY:** StarTech.com offers 24 hour technical support and has been the choice of IT professionals for 30 years, conducting thorough compatibility and performance testing on all our products

Hardware

Warranty	Lifetime
Frame Type	Steel
U Height	1U
Cable Management	No
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity (Stationary)	44.2 lb [20 kg]
------------------------------	-----------------


Special Notes / Requirements

Note	Includes 4x C-cup washers
------	---------------------------

Physical Characteristics

Color	Black
Material	Steel
Internal Width	17.1 in [43.5 cm]
Product Length	9.8 in [25 cm]
Product Width	17.3 in [44 cm]
Product Height	1.7 in [43 mm]
Weight of Product	4.0 lb [1.8 kg]

Packaging Information



Flat Pack (Assembly Required)	No
Package Length	20.9 in [53 cm]
Package Width	10.8 in [27.5 cm]
Package Height	2.2 in [57 mm]
Shipping (Package) Weight	5.1 lb [2.3 kg]

What's in the Box

Included in Package	1U Fixed Shelf
	M6 Cage Nuts
	M6 Screws

****Product appearance and specifications are subject to change without notice.***

