

2U 16in Universal Vented Rack Mount Cantilever Shelf - Fixed Server Rack Cabinet Shelf - 50lbs / 22kg

**Product ID:** CABSHELFV



The CABSHELFV 2U 16in Depth Universal Vented Rack Mount Shelf lets you add a compact, 2U shelf to virtually any standard 19-inch server rack or cabinet with front mount options. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Our vented rack shelves improve air flow and help to lower temperatures in the rack. Constructed using SPCC commercial grade cold-rolled steel, this durable fixed rack shelf can hold up to 22kg (50lbs) of equipment - a perfect solution for storing small, non-rackmount equipment, tools, peripherals or accessories in your rack to keep them readily accessible.

Backed by a StarTech.com Lifetime warranty.

## Certifications, Reports and Compatibility

### Applications

- For use with all 19" wide Server Racks and Cabinets
- Supply additional storage space for mission critical hardware and non-rack mount equipment

### Features

- Fits all standard 19" server racks
- SPCC 1.6mm Cold-rolled steel construction
- Front mount design

- Holds up to 22kg (50lbs)
- 2U Vented Rackmount Shelf
- TAA compliant for GSA Schedule purchases

---

#### Hardware

Warranty	Lifetime
Frame Type	Steel
U Height	2U
Cable Management	No
Mounting Options	Front Mount (Front Only)

---

#### Performance

Weight Capacity (Stationary)	50.0 lb [22.6 kg]
------------------------------	-------------------

---

#### Physical Characteristics

Color	Black
Material	Steel
Rail Thickness	0.1 in [1.6 mm]
Product Length	19.0 in [48.3 cm]
Product Width	16.0 in [40.6 cm]
Product Height	3.5 in [88.0 mm]
Weight of Product	5.7 lb [2.6 kg]

---

#### Packaging Information

Package Length	22.3 in [56.6 cm]
Package Width	16.9 in [42.8 cm]
Package Height	4.3 in [10.8 cm]
Shipping (Package) Weight	7.5 lb [3.4 kg]



---

**What's in the  
Box**

Included in Package	2U Fixed Rack Shelf
	M5 Cage Nuts
	M5 Screws
	Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***

