

## 4 Port CardBus Laptop USB 2.0 PC Card Adapter

**Product ID:** CB420USB



This 4 Port CardBus Laptop USB 2.0 Adapter Card adds four USB 2.0 ports to a laptop computer, providing a cost-effective and simple way to add USB 2.0 devices to mobile operating environments.

An excellent solution for enhancing the capabilities of your laptop computer by adding external peripherals (e.g. hard drives, CD/DVD burners, printers, etc.), the CardBus USB adapter is backed by StarTech.com's Lifetime Warranty, and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- MP3 players
- Digital cameras
- PDAs
- Portable hard drives
- Mice and keyboards
- External CDR/RWs
- DVD drives
- Flash card readers/writers
- Joysticks

- Printers
- Scanners
- Webcams
- iPod connectivity

## Features

- Easy plug-and-play installation
- Data transfer rates up to 480 Mbits/sec. (40 times faster than USB 1.1)
- Connect up to 127 devices by cascading multiple hubs
- Backward compatible with USB version 1.1
- Provides up to 500 mA of power per port

---

### Hardware

Warranty	Lifetime
Ports	4
Interface	USB 2.0
Bus Type	CardBus (PCMCIA)
Chipset ID	VIA/VLI - VT6212

---

### Performance

Maximum Data Transfer Rate	480 Mbps
----------------------------	----------

---

### Connector(s)

Connector Type(s)	PC Card (Type II, Cardbus) USB Type-A (4 pin) USB 2.0
-------------------	--

---

### Software

OS Compatibility	Windows 98SE/ ME/ 2000/ XP (32/64-bit)/ Server 2003 (32/64-bit)/ Vista (32/64-bit)/ 7 (32/64-bit), Mac OS X (tested up to 10.4)
------------------	---

---

### Physical Characteristics



Color	Black
Product Length	4.7 in [12 cm]
Product Width	2.2 in [55 mm]
Product Height	1.0 in [25 mm]
Weight of Product	7.8 oz [220 g]

---

**Packaging Information**

Package Length	5.8 in [14.8 cm]
Package Width	3.1 in [78 mm]
Package Height	9.6 in [24.5 cm]
Shipping (Package) Weight	7.1 oz [200 g]

---

**What's in the Box**

Included in Package	4 Port USB 2.0 CardBus
	USB to DC Power Cable
	Driver CD
	Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***

