

100 Adhesive Cable Management Clips Black - Network/Ethernet/Office Desk/Computer Cord Organizer - Sticky Cable/Wire Holders - Nylon Self Adhesive Clamp UL/94V-2 Fire Rated

Product ID: CBMCC2



These self adhesive one-piece black cable clamps provides an easy way to secure and organize cables in multiple locations. 100 Black cable clips are included, ensuring you'll have plenty on hand.

The cable clips support a 0.47 in. (12 mm) cable bundle diameter and mount to any wall with the included 3M adhesive backing. There's also a 0.21 in. (5.3 mm) mounting hole for added strength. The one-piece cable clamp can be opened and repurposed with different cables.

Made of durable black nylon 66 material and featuring a strong 3M adhesive sticky backing these cable holders are UL94 V-2 fire rated at up to 85C.

To suit any application, StarTech.com offers a selection of these cable clamps in different sizes:

Small Cable Clamps (CBMCC1)

Medium Cable Clamps (CBMCC2)

Large Cable Clamps (CBMCC3)

These cable clamps are TAA compliant and backed by a StarTech.com Lifetime warranty and free 24/5 technical support. StarTech.com has been the IT professionals choice for over 30 years.

Certifications, Reports and Compatibility

Applications

- secure, organize and route cables in your workspace

Features

- **100 PACK SELF ADHESIVE CABLE MANAGEMENT CLIPS:** Keep cables organized w/ cable clamps for 0.47 in. (12 mm) bundle diameter; Install w/ 3M adhesive backing & 0.21" (5.3 mm) mounting hole for added strength
- **INDUSTRIAL STRENGTH:** Made of durable black nylon 66 material; Featuring a strong 3M adhesive sticky backing these cable holders are UL94 V-2 fire rated at up to 85C; Lifetime Warranty
- **VERSATILE:** Multi-purpose cable organizers for power, coax, telephone, audio, video, network, Ethernet, computer, office desk, data cables & wires sticking to metal, wood, drywall & glass surfaces
- **RELIABLE & SAFE:** 70C/158F Temperature Rated Adhesive Backing 94V-2 Flammability Rating UL Approved
- **MULTI-LENGTH:** Also available in small (CBMCC1) for 0.21" (5.5 mm) bundle diameter w/ 0.21" (5.3 mm) mounting hole & large (CBMCC3) for 0.67" (17 mm) bundle diameter w/ 0.19" (4.8 mm) mounting hole

Performance

Warranty	2 Years
General Specifications	Mounting Hole Size: 0.21 in [5.3 mm]

Physical Characteristics

Color	Black
Material	Nylon 66
Product Length	0.7 in [17.0 mm]
Product Width	1.4 in [35.0 mm]
Product Height	0.7 in [19.0 mm]
Weight of Product	0.1 oz [3.3 g]

Packaging Information

Package Length	8.5 in [21.5 cm]
Package Width	10.6 in [27.0 cm]
Package Height	0.4 in [10.0 mm]
Shipping (Package) Weight	12.4 oz [350.0 g]

What's in the Box

Included in Package	Cable Clips
---------------------	-------------

****Product appearance and specifications are subject to change without notice.***

