


100 Pack Cable Tie Mounts with Adhesive Tape for 0.13 in. (3.2 mm) Wide Ties - Nylon/Plastic Zip Tie Mounts - Electrical/Network Cable Wrap Mounts / 94V-2 Fire & UL Rated TAA

Product ID: CBMCTM1



These small cable tie mounts with adhesive backing enable you to conveniently mount your zip ties to secure your cable bundle to the wall or ceiling, to route and organize them. 100 White cable tie mounts are included, ensuring you'll have plenty on hand.

These plastic electrical cable wrap mounts work with cable ties up to 0.13 in. (3.2 mm) in width, at any length.

They're quick and easy to install, simply peel off the protective backing and stick it to your desired location on any surface, including plastic, metal, drywall, wood, or masonry. Once the mount is in place, you can feed the cable tie through the slot, position your cable bundle inside the tie and close the cable tie to secure both the cable bundle and the cable tie to the mount.

This clean and professional cable tie mounting system is perfect for organizing and routing network cables, power cables, or other cables in your office or server room.

Made of durable Nylon 66 material and featuring a strong 3M adhesive sticky backing these cable tie mounts are UL94 V-2 fire rated, and UL Approved.

StarTech.com offers a variety of cable ties that are supported by these mounts:

100 Pack 4 in. (101.6 mm) White Cable Ties (CBMZT4N)

1000 Pack 4 in. (101.6 mm) White Cable Ties (CBMZT4NK)

100 Pack 4 in. (101.6 mm) Black Cable Ties (CBMZT4B)

1000 Pack 4 in. (101.6 mm) Black Cable Ties (CBMZT4BK)

These cable wrap mounts are backed by a StarTech.com Lifetime warranty and free 24/5 technical support. StarTech.com has been the IT professionals choice for over 30 years.

Certifications, Reports and Compatibility

Applications

- Mount zip ties to wall or ceiling to keep cables organized in your office or server room

Features

- **100 PACK OF CABLE TIE MOUNTS:** Mounts zip ties to wall or ceiling to keep cables organized; Works with 0.13 in. (3.2 mm) wide zip ties at any length; Mounts using adhesive tape or built-in screw hole
- **INDUSTRIAL STRENGTH:** Made of durable Nylon 66 material, these tough, cable tie mounts are UL94 V-2 fire rated
- **REDUCE CLUTTER:** Easy to install, these small plastic electrical cable wrap mounts are ideal for reorganizing cable management in your office or server room; Backed for life by StarTech.com
- **RELIABLE SAFETY:** 94V-2 Flammability Rating UL Approved RoHS TAA Compliant
- **MULTI-SIZE:** Available in Medium (CBMCTM2) for cable ties 0.18 in. (4.6 mm) wide and Large (CBMCTM3) for cable ties 0.21 in. (5.5 mm) wide

Performance

Warranty	2 Years
General Specifications	Maximum Cable Tie Width: 0.12 in. (2.3 mm)

Physical Characteristics

Color	White
Material	Nylon 66
Product Length	0.5 in [13 mm]
Product Width	0.5 in [13 mm]
Product Height	0.1 in [3 mm]
Weight of Product	0.0 oz [0.2 g]

Packaging Information

Package Length	6.3 in [16 cm]
----------------	----------------



Package Width	4.5 in [11.5 cm]
Package Height	0.0 in [0.0 mm]
Shipping (Package) Weight	1.1 oz [30 g]

What's in the Box

Included in Package	Cable Tie Mounts
---------------------	------------------

****Product appearance and specifications are subject to change without notice.***

