

Cable Management Raceway 78in - Single Channel Network Cable Hider Kit - Solid Wall Wire Duct System - Power Cord Concealer - Surface Mount Wiring Channel PVC UL Rated

Product ID: CBMWD3816



This 78 in. (2 m) cable management raceway neatly routes cables in your office or server room, while also concealing them to create a tidy and professional look.

This cable management raceway protects cables from damage while neatly routing them in your office or server room. The raceway is 0.63 in. (16 mm) x 1.49 in. (38 mm).

Made from self extinguishing PVC, that's sturdy and warp proof this network/power cable hider/concealer is M1 Rating NF fire resistant with a 186F (86C) Vicat softening point and are UL/94V-0 Rated.

The cable raceway can be mounting by simply drilling holes through housing and into any surface, or double sided tape can used to secure the raceway (screws and tape not included).

To combine and route this cable management raceway and cap off the ends, StarTech.com offers a wide selection raceway accessories.

The Coupler (CBMWD3816C) (20-Pack), joins two raceways together and extends the length of your raceway.

The End Piece (CBMWD3816E) (20-Pack), cleanly caps off the end of your raceway.

The Inside Elbow (CBMWD3816I) (20-Pack), joins two raceways together inside of corners at a 90 degree angle.

The Lateral Elbow (CBMWD3816L) (20-Pack), joins two raceways together and runs them up the wall at a 90 degree angle.

The Outside Elbow (CBMWD3816O) (20-Pack), joins two raceways together around corners at a 90 degree angle.

The T Connector (CBMWD3816T) (20 Pack), joins three raceways together in a T-bar.

This cable management raceway is TAA compliant and backed by a StarTech.com Lifetime warranty and free 24/5 technical support. StarTech.com has been the IT professionals choice for over 30 years.

Certifications, Reports and Compatibility

Applications

- Protects cables from damage while neatly routing them in your office or server room

Features

- **PROFESSIONALLY ORGANIZE & ROUTE CABLES:** Cable management raceway protects 12-30 cables from damage/debris w/closed design & route them in office/server room install by drilling holes/double sided tape
- **INDUSTRIAL STRENGTH:** Sturdy warp-proof, self extinguishing PVC, solid network/power cable hider/concealer is M1 Rating NF fire resistant w/186F Vicat softening point; UL/94V-0 Rated; UL/CSA approved
- **TECHNICAL SPECIFICATIONS:** Length: 78" (2m) Height: 0.63" (16mm) Width: 1.49" (38mm) Max Cable Capacity: 12-30 (subject to thickness) Single Channel Vicat Softening Point: 186F/86C White RoHS
- **STARTECH.COM ADVANTAGE:** IT professionals choice for over 30 years; This surface mount cord kit/ single channel wiring duct system is backed for life by StarTech.com, including free 24/5 tech support
- **RACEWAY ACCESSORIES:** Coupler (CBMCWD3816C), End Piece (CBMCWD3816E), Inside Elbow (CBMCWD3816I), Lateral Elbow (CBMCWD3816L), Outside Elbow (CBMCWD3816O), T Connector (CBMCWD3816T); sold separately

Physical Characteristics

Warranty	2 Years
Color	White
Material	PVC
Product Length	1.5 in [38.0 mm]
Product Width	6.6 ft [2.0 m]
Product Height	0.6 in [16.0 mm]
Weight of Product	15.0 oz [424.0 g]

Packaging Information

Package Length	1.5 in [38.0 mm]
Package Width	6.6 ft [2.0 m]

Package Height 0.6 in [16.0 mm]

Shipping (Package) Weight 15.0 oz [424.0 g]

What's in the Box

Included in Package Raceway

****Product appearance and specifications are subject to change without notice.***

