

## 2 Port CardBus Laptop USB 2.0 PC Card Adapter

**Product ID:** CBUSB22



This 2 Port CardBus USB 2.0 Adapter adds two USB 2.0 ports to your laptop or desktop computer, with support for full hi-speed USB data transfer rates of up to 480 Mbps.

The USB 2.0 CardBus adapter offers backward compatibility with USB 1.1 devices, ensuring seamless operation with older USB peripherals and supports hot-swappable operation to provide hassle-free peripheral connections without having to reboot the computer.

Designed to provide a permanent USB 2.0 solution, the CardBus adapter is backed by StarTech.com's Lifetime Warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Connect all kinds of external USB devices such as cameras, external hard drives, keyboards/mice to a laptop computer
- Add additional USB ports to a laptop to connect more devices
- Upgrade an old laptop with only USB 1.1 ports to be able to use USB 2.0 devices

### Features

- High Speed USB 2.0 compliant host interface, with supported transfer rates up to 480 Mbps
- Backwards compatible with USB 1.1/1.0 devices

- Provides up to 500mA of power per port, with optional external power adapter
- Support for up to 127 USB devices per port (requires additional USB hubs)
- Plug and Play and Hot Swap compatible

---

#### Hardware

Warranty	Lifetime
Ports	2
Interface	CardBus
Bus Type	CardBus (PCMCIA)
Chipset ID	VIA/VLI - VT6212

---

#### Performance

Maximum Data Transfer Rate	480 Mbps
----------------------------	----------

---

#### Connector(s)

Connector Type(s)	USB Type-A (4 pin) USB 2.0 PC Card (Type II, Cardbus)
-------------------	--

---

#### Software

OS Compatibility	Windows 2000, XP, Vista, 7 Windows Server 2003, 2008 R2 Mac OS X 10.10, 10.4.x, 10.3.x, 10.2.x Linux 3.5.x to 4.11.x <i>LTS versions only</i>
Microsoft WHQL Certified	Yes

---

#### Special Notes / Requirements

System and Cable Requirements	Minimum Processor Requirements: Intel Pentium Pro, Pentium III, P4, or better
-------------------------------	---

---

#### Power

Power Source	Not Included (not required for standard applications)
Output Voltage	5 DC
Output Current	1A+



Center Tip Polarity	Positive
---------------------	----------

Plug Type	H
-----------	---

---

**Environmental**

Operating Temperature	0C to 85C (32F to 185F)
-----------------------	-------------------------

Storage Temperature	-55C to 125C (-67F to 257F)
---------------------	-----------------------------

---

**Physical Characteristics**

Product Length	4.5 in [11.5 cm]
----------------	------------------

Product Width	2.2 in [55 mm]
---------------	----------------

Product Height	0.6 in [15 mm]
----------------	----------------

Weight of Product	1.8 oz [50 g]
-------------------	---------------

---

**Packaging Information**

Package Length	8.3 in [21 cm]
----------------	----------------

Package Width	1.6 in [40 mm]
---------------	----------------

Package Height	5.7 in [14.5 cm]
----------------	------------------

Shipping (Package) Weight	4.9 oz [140 g]
---------------------------	----------------

---

**What's in the Box**

Included in Package	CardBus USB 2.0 Card
---------------------	----------------------

Driver CD
-----------

Instruction Manual
--------------------

---

***\*Product appearance and specifications are subject to change without notice.***

