

3ft (91cm) USB4 Cable, 40Gbps, USB-IF Certified USB-C Cable, 240W PD, 8K 120Hz/4K 240Hz DP2.1 DP40 DSC1.2a, TPE Jacket, Thunderbolt 4 Compatible - Black USB-C Cord

Product ID: CC3FT40GUSB4TP



Connect reliably to USB Type-C (USB4), Thunderbolt, and PCIe-enabled devices, delivering up to 40Gbps, 8K/4K video, and 240W of Power Delivery. Each connector is laser-etched with USB4 specifications, an exclusive feature that eliminates guesswork, confirms compatibility, and verifies full USB4 performance.

Safely power high-performance laptops and USB-C devices with up to 240W of Extended Power Range (EPR) Power Delivery 3.1 using a compatible USB-C docking station or wall charger. An integrated E-marker chip ensures accurate power negotiation for stable, consistent charging. Ideal for professional laptops such as Apple M-series Pro/Max MacBooks

Enable full-speed, spec-compliant USB4 performance with a USB-IF Certified cable designed for demanding power, data, and display applications. Rigorously tested to meet electrical and mechanical standards, it ensures reliable interoperability, signal integrity, and consistent operation across a wide range of USB-C devices.

Drive sharp 8K 60Hz video or dual 4K 120Hz displays via DisplayPort 2.1 Alt Mode with DSC, HBR3, and HDR10+ support. Suitable for professional 3D rendering, high-frame-rate video, and bandwidth-intensive visual workflows. This USB4 cable integrates seamlessly with USB-C or Thunderbolt 4 docks, and maintains backward compatibility with a wide range of resolutions and refresh rates. The 3-foot (91cm) cable length is suitable for portable USB-C monitors and desktop workstations.

Certifications, Reports and Compatibility



Applications

- Designed for seamless operation with USB-C or Thunderbolt 4 docking stations
- Drive sharp 8K 60Hz video or support dual 4K 120Hz UHD displays with DSC
- Transfer data at 40 Gbps speeds and 240W of power over a USB4 connection
- Power and charge USB4/USB-C, and Thunderbolt devices

Features

- **Versatile USB4 Performance:** Enhance productivity with full USB4 capabilities, featuring 8K 120Hz video, 40Gbps, and 240W charging over a single connection; Ideal for portable USB-C displays, mobile workstations, and high-speed USB-C devices
- **Safe, Certified Compatibility:** Trust this USB-IF Certified Cable to ensure peak USB4 performance in critical workflows, with E-marker chip for safe and consistent Power Delivery to USB-C devices; Certified cables guarantee USB4 and backward compatibility
- **Identify Specs Instantly:** Swiftly identify this USB4 cable with Quick ID connector markings; The eco-friendly TPE jacket is flexible and durable, designed to withstand tight bends and is fully RoHS-compliant; Shielded 30/32AWG wire protects against EMI
- **Ultra-Fast Docking Cable:** Designed to work with USB-C or Thunderbolt 4 docks; Drive an 8K 120Hz or dual 4K 240Hz displays via DP2.1 (DP40) w/DSC for professional 3D imaging; Ideal for high-performance laptops such as Apple M-series Pro/Max MacBooks
- **The IT Pro's Choice:** Our USB-C cables are rigorously tested in our in-house Innovation Lab for reliable performance, durable construction, and broad compatibility with a variety of devices; Backed by free lifetime 24/5 multi-lingual technical assistance

General

UPC	065030923705
Warranty	Lifetime

Power

Power Delivery	240W
Input Current	5A

Physical & Environmental

Color	Black
Material	TPE
Connector Style	Straight
Wire Gauge	30/32 AWG

Cable Length	36.0 in [914.4 mm]
Cable OD	0.2 in [5.2 mm]
Product Length	36.5 in [928.3 mm]
Product Width	0.5 in [12.3 mm]
Product Height	0.3 in [6.4 mm]
Weight of Product	1.9 oz [53 g]
Operating Temperature	0°C to 60°C (32°F to 140°F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	40 - 65% RH

Performance

HDR Support	HDR10+
Maximum Data Transfer Rate	40 Gbps
Type and Rate	USB4 (40Gbps)
Supported Protocols	USB4 USB 3.2 DisplayPort 2.1 (DP40) Alt Mode Power Delivery 3.1 EPR ,
Audio Specifications	DisplayPort - 32 Channel Audio
Maximum Digital Resolutions	8K 60Hz
Video Revision	DisplayPort 2.1

Hardware

Active or Passive Adapter	Passive
Connector Plating	Nickel
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Copper Foil with Braid

Packaging & In-the-Box

Included in Package	1 - USB4 Cable - 40Gbps
Package Width	6.3 in [160 mm]
Package Depth	7.9 in [200 mm]
Package Height	6.3 in [160 mm]
Shipping (Package) Weight	2.0 oz [57.5 g]

Connector(s)

Connector 1 (Quantity)	1
Connector 1	USB-C (40Gbps, 100W PD Input)
Connector 2 (Quantity)	1
Connector 2	USB-C (40Gbps, 100W PD Input)

****Product appearance and specifications are subject to change without notice.***