

## USB-C to VGA and HDMI Adapter - 2-in-1 - 4K 30Hz - Space Grey

Product ID: CDP2HDVGA



This USB-C to VGA and HDMI adapter offers a portable solution for connecting your USB Type-C laptop to a VGA or HDMI display. The multiport video adapter also works as a splitter, enabling you to simultaneously output an identical video signal to two separate monitors (1 x HDMI and 1 x VGA).

Avoid the hassle of carrying different adapters, with a 2-in-1 USB-C monitor adapter. With VGA, and HDMI outputs, you can conveniently connect your laptop to any HDMI or VGA-equipped display, using this multiport adapter.

The adapter features a durable aluminum enclosure and can withstand being carried in your travel bag.

The HDMI output on this USB-C video adapter supports UHD resolutions up to 4K 30Hz, while the VGA output supports HD resolutions up to 1920 x 1200.

The USB-C video adapter has a Space Gray housing and built-in USB-C cable designed to match your Space Gray MacBook or MacBook Pro. The adapter is compatible with USB-C DP Alt Mode devices.

CDP2HDVGA is backed by a StarTech.com 3-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Connect to virtually any VGA or HDMI display while traveling
- Use as a video splitter to output an identical image to a VGA and HDMI monitor simultaneously splitting the image
- Output video to a secondary VGA, or HDMI monitor

## Features

- Maximize your laptop's video compatibility with a 2-in-1 adapter: USB-C to HDMI and VGA
- Support resource-demanding applications with UHD resolutions up to 4K 30Hz
- Space Gray adapter matches your Space Gray MacBook or MacBook Pro

|                                     |                                   |   |
|-------------------------------------|-----------------------------------|---|
| <b>Hardware</b>                     | Warranty                          | 3 Years   |
|                                     | Active or Passive Adapter         | Active  |
|                                     | AV Input                          | USB-C   |
|                                     | AV Output                         | HDMI - 1.4  |
|                                     | AV Output                         | VGA   |
|                                     | Chipset ID                        | ITE - IT6222  |
| <b>Performance</b>                  | Maximum Cable Distance To Display | 49.9 ft [15.2 m]  |
|                                     | Video Revision                    | HDMI 2.0  |
|                                     | Maximum Analog Resolutions        | 1920 x 1200 @ 60Hz (VGA)<br>3840 x 2160 @ 30Hz (HDMI)   |
|                                     | Maximum Digital Resolutions       | Maximum HDMI output:3840 x 2160 @ 30Hz  |
|                                     | Supported Resolutions             | Maximum VGA output: 1920 x 1200 @ 60Hz  |
|                                     | Audio Specifications              | HDMI - 7.1 Channel Audio  |
|                                     | MTBF                              | 1,576,016 hours   |
|                                     |                                   |   |
| <b>Connector(s)</b>                 | Connector A                       | USB-C (24 pin) DisplayPort Alt Mode   |
|                                     | Connector B                       | VGA (15 pin, High Density D-Sub)  |
|                                     | Connector B                       | HDMI (19 pin)   |
| <b>Special Notes / Requirements</b> | Note                              | HDMI and VGA can output video at the same time. If both video outputs are connected, they'll display the same image at a maximum resolution of 1920x1200 @ 60Hz |
|                                     | Note                              | Maximum Cable Distance to Display refers to digital video. VGA distance capabilities are dependent upon the quality of your cabling                             |
| <b>Environmental</b>                | Operating Temperature             | 0C to 45C (32F to 113F)   |
|                                     | Storage Temperature               | -10C to 70C (14F to 158F)   |

Humidity 5~90% RH

---

**Physical Characteristics**

|                   |                    |
|-------------------|--------------------|
| Color             | Space Gray         |
| Accent Color      | Black              |
| Material          | Aluminum           |
| Cable Length      | 6.6 in [1.7 cm]    |
| Product Length    | 8.1 in [2.0 cm]    |
| Product Width     | 2.4 in [62.000 mm] |
| Product Height    | 0.6 in [15.000 mm] |
| Weight of Product | 1.5 oz [43.000 g]  |

---

**Packaging Information**

|                           |                    |
|---------------------------|--------------------|
| Package Length            | 7.0 in [1.8 cm]    |
| Package Width             | 3.1 in [80.000 mm] |
| Package Height            | 0.8 in [20.000 mm] |
| Shipping (Package) Weight | 2.2 oz [62.000 g]  |

---

**What's in the Box**

|                     |                    |
|---------------------|--------------------|
| Included in Package | Travel A/V Adapter |
|---------------------|--------------------|

---

***\*Product appearance and specifications are subject to change without notice.***

