

6 ft. (1.8 m) USB-C to Mini DisplayPort Cable - 4K 60Hz - Black

**Product ID:** CDP2MDPMM6B



<br>

This USB-C to Mini DisplayPort cable lets you connect your Thunderbolt 3 or USB Type-C enabled device to a Mini DP monitor with just one cable, for a convenient, clutter-free connection.

Harness the video capabilities that are built into your USB-C connection. The USB Type-C to Mini DisplayPort cable delivers the astonishing quality of Ultra HD to your 4K display, at resolutions up to 3840 x 2160. Plus, the adapter is backward compatible with 1080p displays, which makes it a great accessory for home, office or other work environments.

At 6 ft. (1.8 m) in length, this Mini DP cable delivers a compact connection that eliminates excess adapters and cabling, ensuring a tidy, professional installation. For shorter installations, we also offer a 1 m (3.3 ft.) USB C to mDP cable, enabling you to choose the right cable length for your custom installation needs.

For easy operation and installation, this USB 3.1 Type-C to Mini DP adapter cable supports plug-and-play installation on both Windows and Mac computers.

CDP2MDPMM6B is backed by a 3-year StarTech.com warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Connect your MacBook or USB-C device to an mDP monitor
- Ideal for home office or hot desk environments
- Experience crisp visuals with support for 4K 60Hz

- Deliver enriched presentations on the go

## Features

- Reduce clutter with a USB-C to mDP adapter and cable in one
- Get astonishing picture quality with support for UHD video resolutions up to 4K 60Hz
- Make the perfect connection with a Mini DisplayPort cable that works with any USB Type-C enabled device
- Hassle-free connectivity with the reversible USB-C connector
- Compatible with Thunderbolt 3 and USB 3.1 Type-C ports that support DP Alt Mode

---

### Prominence

Warranty	3 Years
Description CDW 75 - 1st Line	StarTech.com 6ft 1.8m USB-C to Mini DisplayPort Cable 4K 60Hz USB C to mDP

---

### Hardware

AV Input	USB-C
Ports	1
AV Output	Mini DisplayPort - 1.2
Chipset ID	STMicroelectronics - STM32F072CBU6

---

### Performance

Maximum Digital Resolutions	3840x2160 @ 60 Hz
Supported Resolutions	1024x768 1280x720 (High-definition 720p) 1920x1080 (High-definition 1080p) 1920x1200 2560x1440 2560x1600 3840x2160 (Ultra HD 4K)
Wide Screen Supported	Yes
Audio Specifications	DisplayPort - 5.1 Channel Audio


---

### Connector(s)

Connector A	USB-C (24 pin) DisplayPort Alt Mode
Connector B	Mini-DisplayPort (20 pin)

---

### Special Notes /



## Requirements

Note Your USB-C port must support DisplayPort over USB-C (DP Alt mode) in order to work with this adapter.

---

## Environmental

Operating Temperature	5C to 35C (41F to 95F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	25%-60%RH

---

## Physical Characteristics

Color	Black
Cable Length	6.0 ft [1.8 m]
Product Length	8.5 in [21.5 cm]
Product Width	0.8 in [20 mm]
Product Height	0.4 in [10 mm]
Weight of Product	2.0 oz [58 g]

---

## Packaging Information

Package Length	8.7 in [22 cm]
Package Width	0.5 in [12 mm]
Package Height	0.3 in [8 mm]
Shipping (Package) Weight	1.8 oz [52 g]

---

## What's in the Box

Included in Package	USB-C to Mini DisplayPort cable
---------------------	---------------------------------

---

***\*Product appearance and specifications are subject to change without notice.***

