

USB C Multiport Video Adapter with HDMI, VGA, Mini DisplayPort or DVI - USB Type C Monitor Adapter to HDMI 1.4 or mDP 1.2 (4K) - VGA or DVI (1080p) - Rose Gold Aluminum

Product ID: CDPVDHMDPRG



This rose gold USB-C multiport video adapter offers a portable solution for connecting your USB Type-C laptop to a VGA, DVI, HDMI or Mini DisplayPort display. The adapter is also available in silver (CDPVGDVHMDMP) and space gray (CDPVDHMDMPSG).

Avoid the hassle of carrying different adapters for different displays with this 4-in-1 USB-C adapter. With VGA, DVI, HDMI and mDP output, you can connect your laptop to virtually any display, a convenient plug-and-play solution for travel or Bring Your Own Device (BYOD) applications.

The HDMI and mDP outputs on this USB-C video adapter support UHD 4K resolutions, providing four times the picture quality of high-definition 1080p. All of the outputs (HDMI, mDP, VGA, DVI) can support high-definition resolutions of up to 1920 x 1200.

The USB Type-C adapter has an aluminum housing designed to match your rose gold MacBook and is compatible with any device that supports USB-C DP Alt Mode. Featuring a built-in USB-C cable with magnetic cable manager, the USB-C video adapter conveniently stores away for easy travel.

The CDPVDHMDPRG is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Connect to virtually any display while traveling
- Connect your BYOD MacBook to a VGA, DVI, HDMI or mDP display at work or school
- Connect a secondary VGA, DVI, HDMI or mDP monitor to your MacBook

Features

- **4-IN-1 MULTIPORT USB-C VIDEO ADAPTER:** USB-C DP Alt Mode to any one of HDMI 1.4 (4K 30Hz & 7.1ch audio), mDP 1.2 (4K 60Hz & 2ch audio), VGA or DVI (1080p), HDCP 2.2/1.4, Thunderbolt 3 compatible
- **TOUGH & PORTABLE:** Durable aluminum Rose Gold enclosure with a magnetically-secured hideaway cable wrap for on-the-go users in the office, at home, boardrooms, and classrooms
- **COMPATIBILITY:** USB-C display adapter for Dell XPS/Precision/Latitude, Lenovo ThinkPad X1 Carbon/Extreme, Surface Laptop 3/Surface Book 3, TB3 MacBook Pro/Air, HP EliteBook/Spectre/ZBook, Chromebooks
- **TESTED & VERIFIED:** USB Type-C adapter tested @ 4K mini DisplayPort (60Hz)/HDMI (30Hz) or 1080p VGA/DVI with TV, monitor & projector brands like Dell, Asus, Acer, LG, Samsung, Sharp, Sony, Epson
- **EASY TO USE:** Supporting a driverless plug-and-play setup, this adapter is fully compatible with multiple OS platforms: Windows / macOS / Linux / Chrome OS

Hardware

Warranty	3 Years
Active or Passive Adapter	Active
AV Input	USB-C
AV Output	HDMI - 1.4 DVI-I (Digital Only) - Single-Link VGA Mini DisplayPort - 1.2
Chipset ID	Cypress - CYPD1120 Cypress - CY7C65210 Parade - PS8348B Parade - PS171

Performance

Maximum Cable Distance To Display	49.9 ft [15.2 m]
Maximum Analog Resolutions	1920 x 1200 @ 60Hz
Maximum Digital Resolutions	3840 x 2160 @ 30Hz

Supported Resolutions	<p>Max HDMI output: 3840 x 2160 @ 30Hz</p> <p>Max mDP output: 3840 x 2160 @ 60Hz</p> <p>HDMI and mDP output: 3840 x 2160, 2560 x 1600, 1920 x 1200, 1920 x 1080, 1280 x 720</p> <p>DVI and VGA output: 1920 x 1200, 1920 x 1080, 1280 x 720</p>
Wide Screen Supported	Yes
Audio Specifications	<p>HDMI - 7.1 Channel Audio</p> <p>DVI - No Audio Support</p> <p>VGA - No Audio Support</p> <p>Mini DisplayPort - 5.1 Channel Audio</p>
MTBF	654,111 hours

Connector(s)

Connector A	USB-C (24 pin) DisplayPort Alt Mode
Connector B	<p>Mini-DisplayPort (20 pin)</p> <p>VGA (15 pin, High Density D-Sub)</p> <p>DVI-D (25 pin)</p> <p>HDMI (19 pin)</p>

Special Notes / Requirements

Note	<p>Only one video output is supported on the video adapter at a time, if multiple connections are made, only one of the outputs will function</p> <p>Maximum Cable Distance to Display refers to digital video. VGA distance capabilities are dependent upon the quality of your cabling</p>
------	--

Environmental

Operating Temperature	0C to 45C (32F to 113F)
-----------------------	-------------------------



Storage Temperature	-10C to 70C (14F to 158F)
Humidity	Storage: 5% ~ 90 % RH (no condensation) Operating: 10% ~ 85 % RH (no condensation)

Physical Characteristics

Color	Rose Gold
Material	Aluminum
Cable Length	4.5 in [11.5 cm]
Product Length	6.7 in [16.9 cm]
Product Width	5.6 in [14.2 cm]
Product Height	0.6 in [15.0 mm]
Weight of Product	6.4 oz [180.0 g]

Packaging Information

Package Length	2.2 in [55.0 mm]
Package Width	4.1 in [10.5 cm]
Package Height	0.6 in [16.0 mm]
Shipping (Package) Weight	3.5 oz [100.0 g]

What's in the Box

Included in Package	travel A/V adapter
---------------------	--------------------

**Product appearance and specifications are subject to change without notice.*

