

USB-C Multiport Video Adapter - 3-in-1 - 4K 30Hz - Black

**Product ID:** CDPVGDVHDBP



This USB-C multiport video adapter offers a portable solution for connecting your USB Type-C laptop to a VGA, DVI or HDMI display.

Avoid the hassle of carrying different adapters for different displays with this 3-in-1 USB-C adapter. With VGA, DVI and HDMI output, you can connect your laptop to virtually any display.

The HDMI output on this USB-C video adapter supports UHD 4K resolutions, providing four times the picture quality of high-definition 1080p. All of the outputs (HDMI, VGA, DVI) can support high-definition resolutions of up to 1920 x 1200.

The convenient plug-and-play USB-C dongle is the perfect travel accessory. Fitting easily into your laptop bag, and offering three video output options, the USB-C display adapter is an ideal solution for Bring Your Own Device (BYOD) applications, wherever you go.

The CDPVGDVHDBP is backed by a StarTech.com 3-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Connect to virtually any display while traveling
- Connect your BYOD laptop to a provided VGA, DVI or HDMI display at work or school
- Connect a VGA, DVI or HDMI monitor to your USB-C computer to use as a secondary monitor

### Features

- Maximize your video compatibility with a 3-in-1 USB-C display adapter: USB-C to VGA, DVI, or HDMI
- Get astonishing picture quality with support for UHD resolutions up to 4K 30Hz
- Thunderbolt 3 and USB Type-C with DP Alt Mode Compatible
- Easy to set up, use, and store

---

### Prominence

Warranty	3 Years
Description CDW 75 - 1st Line	StarTech.com USB C to VGA, HDMI or DVI Adapter - USB C Multiport Adapter

---

### Hardware

Active or Passive Adapter	Active
AV Input	USB-C
AV Output	DVI-I (Digital Only) - Single-Link HDMI - 1.4 VGA

---

### Performance

Video Revision	DisplayPort 1.2
Maximum Cable Distance To Display	49.9 ft [15.2 m]
Maximum Analog Resolutions	1920 x 1200 @ 60Hz
Maximum Digital Resolutions	3840 x 2160 @ 30Hz
Supported Resolutions	HDMI output: 3840 x 2160 (@ 30 Hz), 2560 x 1600, 2048 x 1280 (@ 60 Hz), 1920 x 1200, 1920 x 1080, 1280 x 720  VGA and DVI output: 1920 x 1200 (@ 60 Hz), 1920 x 1080, 1280 x 720
Wide Screen Supported	Yes
Audio Specifications	HDMI - 7.1 Channel Audio

DVI - No Audio Support

VGA - No Audio Support

General Specifications Only one video output is supported on the video adapter at a time. If multiple connections are made, only one of the outputs will function.

#### Connector(s)

Connector A	USB-C (24 pin) DisplayPort Alt Mode
Connector B	HDMI (19 pin)
	DVI-I (29 pin)
	VGA (15 pin, High Density D-Sub)

#### Special Notes / Requirements

System and Cable Requirements	Your USB-C port must support DisplayPort over USB-C (DP Alt mode) in order to work with this adapter.
Note	Maximum Cable Distance to Display refers to digital video. VGA distance capabilities are dependent upon the quality of your cabling

#### Environmental

Operating Temperature	0C to 45C (32F to 113F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	10%-85% RH

#### Physical Characteristics

Color	Black
Cable Length	5.9 in [15 cm]
Product Length	3.3 in [85.0 mm]
Product Width	1.8 in [45.0 mm]
Product Height	0.6 in [15.0 mm]
Weight of Product	1.8 oz [51.0 g]

#### Packaging Information

Package Length	8.9 in [22.5 cm]
----------------	------------------



Package Width	4.9 in [12.5 cm]
Package Height	0.8 in [20.0 mm]
Shipping (Package) Weight	1.9 oz [55.0 g]

---

**What's in the Box**

Included in Package	USB-C travel adapter
---------------------	----------------------

---

***\*Product appearance and specifications are subject to change without notice.***

