

## USB-C Multiport Video Adapter- 3-in-1 - 4K 30Hz-Black

Product ID: CDPVGDVHDBP



This USB-C multiport video adapter offers a portable solution for connecting your USB Type-C laptop to a VGA, DVI or HDMI display.

Avoid the hassle of carrying different adapters for different displays with this 3-in-1 USB-C adapter. With VGA, DVI and HDMI output, you can connect your laptop to virtually any display.

The HDMI output on this USB-C video adapter supports UHD 4K resolutions, providing four times the picture quality of high-definition 1080p. All of the outputs (HDMI, VGA, DVI) can support high-definition resolutions of up to 1920 x 1200.

The convenient plug-and-play USB-C dongle is the perfect travel accessory. Fitting easily into your laptop bag, and offering three video output options, the USB-C display adapter is an ideal solution for Bring Your Own Device (BYOD) applications, wherever you go.

The CDPVGDVHDBP is backed by a StarTech.com 3-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Connect to virtually any display while traveling
- Connect your BYOD laptop to a provided VGA, DVI or HDMI display at work or school
- Connect a VGA, DVI or HDMI monitor to your USB-C computer to use as a secondary monitor

## Features

- Maximize your video compatibility with a 3-in-1 USB-C display adapter: USB-C to VGA, DVI, or HDMI
- Get astonishing picture quality with support for UHD resolutions up to 4K30Hz
- Thunderbolt 3 and USB Type-C with DP Alt Mode Compatible
- Easy to set up, use, and store

<b>Hardware</b>	Warranty	2 Years
	Active or Passive Adapter	Active
	AV Input	USB-C
	AV Output	DVI-I (Digital Only) - Single-Link
	AV Output	VGA
	AV Output	HDMI - 1.4
<b>Performance</b>	Maximum Cable Distance To Display	49.9 ft [15.2 m]
	Video Revision	DisplayPort 1.2
	Maximum Analog Resolutions	1920 x 1200 @ 60Hz
	Maximum Digital Resolutions	3840 x 2160 @ 30Hz
	Supported Resolutions	HDMI output: 3840 x 2160 (@ 30 Hz), 2560 x 1600, 2048 x 1280 (@ 60 Hz), 1920 x 1200, 1920 x 1080, 1280 x 720
	Wide Screen Supported	VGA and DVI output: 1920 x 1200 (@ 60 Hz), 1920 x 1080, 1280 x 720
	Audio Specifications	Yes
	Audio Specifications	HDMI - 7.1 Channel Audio
	Audio Specifications	DVI - No Audio Support
	General Specifications	VGA - No Audio Support
		Only one video output is supported on the video adapter at a time. If multiple connections are made, only one of the outputs will function.
<b>Connector(s)</b>	Connector A	USB-C (24 pin) DisplayPort Alt Mode
	Connector B	HDMI (19 pin)
	Connector B	DVI-I (29 pin)
	Connector B	VGA (15 pin, High Density D-Sub)
<b>Special Notes / Requirements</b>	System and Cable Requirements	Your USB-C port must support DisplayPort over USB-C (DP Alt mode) in order to work with this adapter.
	Note	Maximum Cable Distance to Display refers to digital video. VGA distance capabilities are dependent upon the quality of your cabling

---

<b>Environmental</b>	Operating Temperature	0C to 45C (32F to 113F)
	Storage Temperature	-10C to 70C (14F to 158F)
	Humidity	10%-85% RH

---

<b>Physical Characteristics</b>	Color	Black
	Cable Length	5.9 in [1.5 cm]
	Product Length	3.3 in [85.000 mm]
	Product Width	1.8 in [45.000 mm]
	Product Height	0.6 in [15.000 mm]
	Weight of Product	1.8 oz [51.000 g]

---

<b>Packaging Information</b>	Package Length	8.9 in [2.2 cm]
	Package Width	4.9 in [1.2 cm]
	Package Height	0.8 in [20.000 mm]
	Shipping (Package) Weight	1.9 oz [55.000 g]

---

<b>What's in the Box</b>	Included in Package	USB-C travel adapter
--------------------------	---------------------	----------------------

---

*\*Product appearance and specifications are subject to change without notice.*

