

## USB C Multiport Video Adapter with HDMI, VGA, Mini DisplayPort or DVI - USB Type C Monitor Adapter to HDMI 1.4 or mDP 1.2 (4K) - VGA or DVI (1080p) - Silver Aluminum

### **Product ID:** CDPVGDVHMDMP

This silver USB-C multiport video adapter offers a portable solution for connecting your USB Type-C laptop to a VGA, DVI, HDMI or Mini DisplayPort display. The adapter is also available in Space Gray (CDPVDHMDMPDG) and Rose Gold (CDPVDHMDMPRG).

Avoid the hassle of carrying different adapters for different displays with this 4-in-1 USB-C adapter. With VGA, DVI, HDMI and mDP output, you can connect your laptop to virtually any display, a convenient plug-and-play solution for travel or Bring Your Own Device (BYOD) applications.

The HDMI and mDP outputs on this USB-C video adapter support UHD 4K resolutions, providing four times the picture quality of high-definition 1080p. All of the outputs (HDMI, mDP, VGA, DVI) can support high-definition resolutions of up to 1920 x 1200.

The USB Type-C adapter has an aluminum housing designed to match your silver MacBook and is compatible with any device that supports USB-C DP Alt Mode. Featuring a built-in USB-C cable with magnetic cable manager, the USB-C video adapter conveniently stores away for easy travel.

The CDPVGDVHMDMP is backed by a StarTech.com 3-year warranty and free lifetime technical support.

## **Certifications, Reports and Compatibility**

### **Applications**

- Connect to virtually any display while traveling
- Connect your BYOD MacBook to a VGA, DVI, HDMI or mDP display at work or school
- Connect a secondary VGA, DVI, HDMI or mDP monitor to your MacBook

### **Features**

- **4-IN-1 MULTIPORT USB-C VIDEO ADAPTER:** USB-C DP Alt Mode to any one of HDMI 1.4 (4K 30Hz & 7.1ch audio), mDP 1.2 (4K 60Hz & 2ch audio), VGA or DVI (1080p), HDCP 2.2/1.4, Thunderbolt 3 compatible
- **TOUGH & PORTABLE:** Durable aluminum Silver enclosure with a magnetically-secured hideaway cable wrap for on-the-go users in the office, at home, boardrooms, and classrooms
- **COMPATIBILITY:** USB-C display adapter for Dell XPS/Precision/Latitude, Lenovo ThinkPad X1 Carbon/Extreme, Surface Laptop 3/Surface Book 3, TB3 MacBook Pro/Air, HP EliteBook/Spectre/ZBook, Chromebooks
- **TESTED & VERIFIED:** USB Type-C adapter tested @ 4K mini DisplayPort (60Hz)/HDMI (30Hz) or 1080p VGA/DVI with TV, monitor & projector brands like Dell, Asus, Acer, LG, Samsung, Sharp, Sony, Epson
- **EASY TO USE:** Supporting a driverless plug-and-play setup, this adapter is fully compatible with multiple OS platforms: Windows / macOS / Linux / Chrome OS

---

## Hardware

Warranty	3 Years
Active or Passive Adapter	Active
AV Input	USB-C
AV Output	DVI-I (Digital Only) - Single-Link
	VGA
	Mini DisplayPort - 1.2
	HDMI - 1.4
Chipset ID	Cypress - CYPD1120
	Cypress - CY7C65210
	Parade - PS8348B
	Parade - PS171

---

## Performance

Maximum Cable Distance To Display	49.9 ft [15.2 m]
Video Revision	DisplayPort 1.2
	HDMI 1.4
Maximum Analog Resolutions	1920 x 1200 @ 60Hz
Maximum Digital Resolutions	3840 x 2160 @ 30Hz
Supported Resolutions	Max HDMI output: 3840 x 2160 @ 30Hz
	Max mDP output: 3840 x 2160 @ 60Hz
	HDMI and mDP output: 3840 x 2160, 2560 x 1600, 1920 x 1200, 1920 x 1080, 1280 x 720
	DVI and VGA output: 1920 x 1200, 1920 x 1080, 1280 x 720
Wide Screen Supported	Yes



Audio Specifications	HDMI - 7.1 Channel Audio
	VGA - No Audio Support
	Mini DisplayPort - 5.1 Channel Audio
	DVI - No Audio Support
General Specifications	Only one video output is supported on the video adapter at a time. If multiple connections are made, only one of the outputs will function.
MTBF	654,111 hours

---

#### Connector(s)

Connector A	USB-C (24 pin) DisplayPort Alt Mode
Connector B	Mini-DisplayPort (20 pin)
	VGA (15 pin, High Density D-Sub)
	DVI-D (25 pin)
	HDMI (19 pin)

---

#### Special Notes / Requirements

System and Cable Requirements	Your USB-C port must support DisplayPort over USB-C (DP Alt mode) in order to work with this adapter.
Note	Maximum Cable Distance to Display refers to digital video. VGA distance capabilities are dependent upon the quality of your cabling

---

#### Environmental

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	40%-50%RH

---

#### Physical Characteristics

Color	Silver
Cable Length	4.3 in [11 cm]
Product Length	4.1 in [10.5 cm]
Product Width	2.2 in [55 mm]



Product Height 0.6 in [15 mm]

Weight of Product 3.8 oz [108 g]

---

**Packaging  
Information**

Package Length 6.7 in [17 cm]

Package Width 5.7 in [14.5 cm]

Package Height 1.2 in [30 mm]

Shipping (Package)  
Weight 6.5 oz [184 g]

---

**What's in the  
Box**

Included in Package travel A/V adapter

---

***\*Product appearance and specifications are subject to change without notice.***

