

CFast Card to SATA Adapter with 2.5" Housing

Product ID: CFAST2SAT25



Now you can use your CFast memory card like a standard 2.5" SATA solid-state drive. This unique adapter lets you access and recover data from a CFast card through SATA at faster data transfer speeds.

This CFast to SATA adapter creates a permanent conversion from CFast to SATA for use inside small form factor or embedded solutions. The drive frame and the connector on the adapter mimic the exact size and connector location of a 2.5" SATA hard drive.

Standard 2.5" housing allows the converted card to be installed into a laptop or other standard mounting bracket. Once the CFast card is mounted inside this adapter, you can use it just like a 2.5" SATA drive - in your laptop, docking station, enclosure or desktop computer.

Transfer data from your CFast card to your PC through SATA, with file transfer speeds of up to 6 Gbps. You can offload data from your DSLR cameras and camcorders, or transfer graphic design files, videos and other files from your CFast card.

Faster file transfer speeds means you'll spend less time waiting for file transfers to complete. The actual speed will depend on the speed of the CFast media.

Engineered with a durable protective housing, the CFAST2SAT25 adapter is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Access and recover data from a CFAST card quickly through SATA
- Offload data from high-end digital cameras and camcorders, or to transfer graphic design files and videos

Features

- Make your CFast card work like a 2.5in SATA SSD
- Supports SATA III with data transfer speeds of up to 6 Gbps
- SATA and power combo connector (7 + 15 pin) - same as a 2.5" SATA hard drive
- Standard 2.5" housing allows the converted card to be installed into a laptop
- OS independent, with no drivers or software installation required
- Durable protective housing

Hardware

Warranty	2 Years
Interface	SATA
Number of Drives	1
Drive Size	CFast (I/II Card)
Compatible Drive Types	CFAST 2.0, 1.0
Supported Drive Height(s)	3.3mm 5mm

Performance

Maximum Data Transfer Rate	6 Gbps
Type and Rate	SATA III (6 Gbps)
Hardware Raid Supported	No
Insertion Rating	10,000
Memory Media Type	CFast (I/II Card)
MTBF	50,000

Connector(s)

Drive Connectors	CFast Data & Power Combo (7+17 pin)
------------------	-------------------------------------



Host Connectors	SATA Data & Power Combo (7+15 pin)
-----------------	------------------------------------

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Environmental

Operating Temperature	0C to 75C (32F to 167F)
Storage Temperature	-40C to 85C (-40F to 185F)
Humidity	5%~95% RH

Physical Characteristics

Color	Black & Silver
Material	Steel and Plastic
Product Length	3.9 in [99 mm]
Product Width	2.7 in [69 mm]
Product Height	0.4 in [9.9 mm]
Weight of Product	1.9 oz [54 g]

Packaging Information

Package Length	6.6 in [16.7 cm]
Package Width	5.7 in [14.4 cm]
Package Height	1.3 in [32 mm]
Shipping (Package) Weight	3.5 oz [100 g]

What's in the Box

Included in Package	CFAST card to SATA converter
	Assembly screw kit
	Quick install guide

**Product appearance and specifications are subject to change without notice.*