

1U Brush Strip Horizontal Server Rack Cable Management Panel

Product ID: CMBRUSH1U



The CMBRUSH1U Brush Strip Cable Management Panel mounts to a standard 19" 2 or 4-post rack to organize cables while keeping dust and dirt out of the rack. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Constructed of high-quality steel with high-density nylon bristles, the 1U brush plate creates a clean looking point of entry and offers cable separation for simple cable organization. The brush panel also promotes proper airflow through the rack by closing off open spaces between equipment.

For easy installation, this cable organizer comes complete with 2 sets of rack screws (10/32 and 12/24).

Backed by a StarTech.com 2-year warranty.

Certifications, Reports and Compatibility

Applications

- Use with server racks and cabinets, structured wiring closets and network distribution cabling to keep cables neat and tidy

Features

- Sturdy steel construction
- Mounts to standard 19" 2 or 4-post server racks
- Includes rack screws

- High-density nylon brush
- Takes up only 1U of rack space
- TAA compliant for GSA Schedule purchases

Hardware

Warranty	2 Years
U Height	1U
Industry Standards	EIA RS310-D
Orientation	Horizontal
Mounting Options	Front Mount (Front Only)

Physical Characteristics

Color	Black
Material	Steel
Rail Thickness	0.0 in [1.2 mm]
Internal Depth	0.8 in [20.2 mm]
Product Length	19.0 in [48.2 cm]
Product Width	0.7 in [17.2 mm]
Product Height	1.7 in [43.7 mm]
Weight of Product	14.9 oz [421.2 g]

Packaging Information

Package Length	19.3 in [48.9 cm]
Package Width	2.0 in [51.0 mm]
Package Height	1.1 in [28.0 mm]
Shipping (Package) Weight	17.9 oz [506.4 g]

What's in the Box

Included in Package	1U Cable Manager
---------------------	------------------



10/32 Panel Screws

12/24 Panel Screws

****Product appearance and specifications are subject to change without notice.***

