

Multi-Directional Vertical Server Rack Cable Management D-Ring Hook 2.4x3.9in (6x10cm)

Product ID: CMHOOKMW



The CMHOOKMW Multi-Directional Vertical Cable Management D-ring lets you add an internal or external facing cable hook to your server rack or cabinet, to provide an organized channel for cables. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Constructed of high-quality steel, the cable management ring measures 2.4 x 3.9in (6 x 10cm). For flexible mounting options, the cable ring features a right-angled mounting bracket with 2 sets of mounting holes, enabling you to face the D-ring in the direction that best fits your application. Providing strain relief for attached cables, multiple cable rings can be attached to your rack where you need them for a versatile cable management solution.

Backed by a StarTech.com 2-year warranty.

Certifications, Reports and Compatibility

Applications

- Ideal for structured wiring closets and network distribution cabling
- Use with server racks and cabinets to keep cables neat and tidy

Features

- Sturdy steel construction
- 2.4x3.9in (6x10cm) Cable Management Hook
- Right-angled bracket with 2 sets of mounting holes for flexible positioning

- TAA compliant for GSA Schedule purchases

Hardware

Warranty	2 Years
U Height	1.5U
Industry Standards	EIA RS310-D
Orientation	Vertical

Physical Characteristics

Color	Black
Material	Steel
Rail Thickness	0.1 in [2 mm]
Product Length	4.0 in [10.2 cm]
Product Width	2.8 in [70.1 mm]
Product Height	4.4 in [11.1 cm]
Weight of Product	6.1 oz [173.0 g]

Packaging Information

Package Length	5.0 in [12.7 cm]
Package Width	5.0 in [12.7 cm]
Package Height	3.2 in [82.0 mm]
Shipping (Package) Weight	8.8 oz [250.0 g]

What's in the Box

Included in Package	Vertical Cable Management Hook
	10/32 Screws
	24/24 Cage Nuts
	12/24 Screws



****Product appearance and specifications are subject to change without notice.***

