

Composite and S-Video to VGA Video Converter for Computer Monitors

Product ID: COMP2VGA



This Composite and S-Video to VGA Video Converter lets you play console video games on your computer monitor! With StarTech.com's for Computer Monitors Video Game Jockey, there's no more waiting to use the TV. Simply connect your Xbox, Playstation 2, GAMECUBE, Dreamcast, or other game console to the Video Game Jockey, then plug into your computer monitor, and it's game on!

An economical solution that saves the expense of a separate TV and frees up your workspace, the Composite/S-Video to VGA converter supports full audio pass through via your PC speakers or headphones and switches from PC to game display with the push of a button - the adapter even works when the computer is powered off!

A versatile video solution, the Composite/S-Video to VGA converter is also a great way to connect VCRs, DVD players and camcorders to your monitor.

Backed by StarTech.com's 2-year warranty.

Certifications, Reports and Compatibility

Applications

- Connects any commercial game console or VCR/DVD to a VGA monitor

Features

- Convenient push-button switching between game display and PC display
- Easy one-time plug and play set up requires no drivers

- Audio pass through with amplified (active) speakers
- Also allows VCRs, DVDs and video cameras to connect to monitor
- Includes all necessary cables for instant out of the box set up
- Compatible anywhere in the world, with automatic NTSC and PAL video signals detection
- Supports composite (RCA) and S-video input
- Superior video resolution - 1280 x 1024 @ 60Hz

Hardware

Warranty	2 Years
Active or Passive Adapter	Active
AV Input	S-Video Composite
AV Output	VGA
Audio	Yes

Performance

Maximum Analog Resolutions	1280 x 1024
Supported Resolutions	NTSC - 720 x 480 PAL - 720 x 576
Frequency Range	NTSC Horizontal = 31.4685KHz Vertical = 60 Hz PAL Horizontal = 31.25 KHz Vertical = 50 Hz

Connector(s)

Connector A	Stereo Audio (2 x RCA) S-Video (4 pin, Mini-DIN) Composite Video (1 x RCA) 3.5 mm Mini-Jack (3 Position)
-------------	---



Connector B	3.5 mm Mini-Jack (3 Position)
	VGA (15 pin, High Density D-Sub)
	VGA (15 pin, High Density D-Sub)

Special Notes / Requirements

System and Cable Requirements	The SPK out port cannot be used with headphones.
-------------------------------	--

Power

Power Source	AC Adapter Included
Input Voltage	100 ~ 125 AC
Input Current	0.1 A
Output Voltage	9V DC
Output Current	0.6A
Center Tip Polarity	Positive
Power Consumption (In Watts)	5.4

Physical Characteristics

Color	Black
Product Length	6.5 in [16.5 cm]
Product Width	4.0 in [10.1 cm]
Product Height	1.0 in [25 mm]
Weight of Product	1.7 oz [49 g]

Packaging Information

Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	0.4 in [10 mm]
Shipping (Package)	2.0 oz [58 g]



Weight

What's in the Box

Included in Package	Composite/Svideo to VGA Converter
	VGA cable
	3.5mm audio cable
	AC Adapter
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

