

8in Nylon Cable Ties - Pkg of 1000 - TAA

Product ID: CV200K



Our 8in Cable Ties feature durable yet pliable UL-approved Nylon construction.

Certifications, Reports and Compatibility



Applications

Features

Performance

Warranty	2 Years
Minimum Tensile Strength	39.7 lb [18 kg]

Physical Characteristics

Color	White
Materials	UL-approved Nylon 66, 94V-2
Diameter	Max. Bundle - 2.17 in[55 mm]

Product Length	8.0 in [20.3 cm]
Product Width	0.1 in [0.4 cm]
Product Height	0.0 in [0.0 cm]
Weight of Product	1.9 lb [0.9 kg]

Packaging Information

Package Quantity	1000
Package Length	10.8 in [27.5 cm]
Package Width	8.7 in [22.2 cm]
Package Height	4.0 in [10.2 cm]
Shipping (Package) Weight	2.1 lb [0.9 kg]

What's in the Box

Included in Package	1000 - 8 inch Nylon Cable Ties
---------------------	--------------------------------

Warranty Information

Warranty	2 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***