

Handheld Digital Temperature/Humidity Meter, Hygrometer W/Large LCD, Portable Thermometer  
For Server Rooms/Offices, Accurate Sensor, Min/Max Readings

**Product ID:** DH60-THERMOMETER



The Handheld Temperature and Humidity Meter is equipped with a high-precision sensor that provides accurate environmental readings. Its compact and lightweight design makes it easy to carry and use in a variety of environments.

This portable thermometer is capable of precise readings in a temperature range of 14 to 140F (-10 to 60C) and relative humidity (RH) range of 0 to 100% with a resolution of 0.2F (0.1C) and 0.1% RH. Switch between temperature units or view minimum and maximum readings with the press of a button.

The portable hygrometer features an easy-to-read LCD with large fonts for quick, at-a-glance readings, and optional backlight for visibility in low-light conditions. The on-screen battery indicator keeps the user informed, while the five-minute auto-off feature maximizes battery life. The data hold button enables to keep the last reading on the screen for reference.

The temperature tester is ideal for monitoring server rooms, data centers, office environments, and equipment testing by providing real-time data to verify ambient conditions or cooling performance of computer systems.

Made of durable ABS plastic, the digital thermometer is lightweight, compact, and convenient to transport. The non-slip design ensures a secure grip, making it ideal for on-the-go measurements in a variety of work environments.

## Certifications, Reports and Compatibility



## Applications

## Features

- **TEMPERATURE AND HUMIDITY METER:** The handheld digital thermometer features a high-sensitivity sensor with a dew point temperature range of 14 to 140F (-10 to 60C) and relative humidity (RH) range of 0 to 100%; Requires 3x AAA batteries (not included)
- **ACCURATE SENSOR:** Precise temperature and humidity readings with resolution of 0.2F (0.1C) & 0.1% RH; Accuracy of +/- 2F (+/- 1C) & +/- 5% RH; Change temperature units & min/max readings with a button press
- **EASY READOUT:** Features a large-font display for quick, at-a-glance readings, with a data hold function to keep measurements visible, and optional backlight for use in low-light conditions; 5-min auto-off feature maximizes battery life
- **APPLICATIONS:** Monitor the performance of cooling systems and other equipment in real-time by tracking the ambient conditions they operate in; Ideal for use in server rooms, data centers, office environment control, and equipment testing
- **PORTABLE:** Compact and lightweight thermometer and hygrometer tester is easy to store and transport; Made from durable ABS plastic with a non-slip design, ideal for on-the-go measurements in various work environments

---

### Performance

Warranty	2 Years
General Specifications	Min temperature range of 14F (-10C) , Max temperature range of 140F (60C)
	Relative humidity range of 0 and 100% RH
	Resolution of 0.2F (0.1C) & 0.1% RH
	Accuracy of +/- 2F (+/- 1C) & +/- 5% RH

---

### Power

Power Source	Batteries (not included)
--------------	--------------------------

---

### Physical Characteristics

Color	Gray
Material	ABS
Product Length	1.2 in [3.0 cm]
Product Width	2.0 in [5.0 cm]
Product Height	5.7 in [14.5 cm]
Weight of Product	6.7 oz [190.0 g]

---

**Packaging  
Information**

Package Length	1.4 in [3.5 cm]
Package Width	4.2 in [10.6 cm]
Package Height	0.8 in [2.1 cm]
Shipping (Package) Weight	7.1 oz [200.0 g]

---

**What's in the Box**

Included in Package	1 - Digital Thermometer
	1 - Quick-Start Guide

---

***\*Product appearance and specifications are subject to change without notice.***