33ft (10m) Active DisplayPort Cable - 4K Ultra HD DisplayPort Cable - Long DP to DP Cable for Projector/Monitor - DP Video/Display Cord - Latching DP Connectors

**Product ID:** DISPL10MA

The DISPL10MA 10m Active DisplayPort Cable features a built-in active signal booster for a connection distance of up to 30 feet (10m) between your DisplayPort-enabled devices - almost double the DisplayPort connection distance limitation of 16ft, with no signal loss.

This durable yet lightweight active DP cable features a thinner 32 AWG wire construction that allows for a more flexible installation with minimal clutter. Plus, the cable features built-in amplifier circuitry which actively boosts the DisplayPort signal with no external power needed.

The 10m cable offers a bandwidth of 10.8 Gbps with support for maximum resolutions up to WQXGA (25601600) and optional audio support. The cable is both HDCP and DPCP capable, which ensures that digitally protected content is displayed properly.

This 10-meter Active DisplayPort cable is backed by StarTech.com's 2-year Warranty.

Please Note:This cable features unidirectional architecture which requires that the cable is installed in the correct direction. Please refer to the "source" and "display" labels on the DisplayPort connectors, in order to ensure that the display device (monitor, projector etc.) and the DisplayPort source are connected properly.

## Certifications, Reports and Compatibility

## Applications

• Connecting a DisplayPort display to a PC or alternative DisplayPort source , over long distances, with no signal loss

## Features

• LIGHT AND DURABLE CABLE: Long-lasting light-weight cable; 32AWG wire; Flexible PVC jacket; Superior EMI shielding with Al-Mylar foil and copper braid provides higher quality video and audio; Backwards compatible with DP 1.1

• APPLICATIONS: Ideal for home/offices/boardrooms/conference rooms/classrooms, works with your laptop/professional workstations with FirePro S9000/7000, W8100/7100/5100 or R5000 graphic cards; Use with UHD/4K monitors, projector or large display

• SPECS: 10 meter (33 foot)  Black  DisplayPort v1.1a Latching Male to Male  32 AWG  PVC cable jacket  Shield: Al-Mylar foil with Braid  Protocols: HBR, MST, GTC  2-Year Warranty  Note: DP connector labelled "Display" connects to the display side

• ACTIVE CIRCUITRY: Active bus powered amplifier boosts video signals over longer distances up to 10 m (no external power supply needed), supports additional color spaces

• ACTIVE DISPLAYPORT CABLE: Active 10m (32.8ft) DisplayPort cable supports 4K (3840x2160p at 30Hz), 10.8 Gbps bandwidth, HBR, 8Ch Audio, Multi-Stream Transport (MST), GTC for precise audio channel timing & 3D Stereo (1080p at 60Hz)

| | | |
|---|---|---|
| **General** | | |
| | UPC | 065030854221 |
| | Package Quantity | 1 |
| | Warranty | 2 Years |
| **Physical & Environmental** | | |
| | Color | Black |
| | Connector Style | Straight |
| | Wire Gauge | 32 AWG |
| | Cable Length | 32.8 ft [10 m] |
| | Product Length | 32.8 ft [10.0 m] |
| | Product Width | 0.8 in [20.0 mm] |
| | Product Height | 0.5 in [12.0 mm] |
| | Weight of Product | 16.0 oz [452.0 g] |
| | Operating Temperature | 0C to 45C (32F to 113F) |

| | | |
|---|---|---|
| | Storage Temperature | -20C to 70C (-4F to 158F) |
| **Hardware** | | |
| | Number of Conductors | 19 |
| | Connector Plating | Nickel |
| | Cable Jacket Material | PVC (Polyvinyl Chloride) |
| | Cable Shield Material | Aluminum-Mylar Foil with Braid |
| | Fire Rating | CM/CMG (General Purpose) |
| **Packaging & In-the-Box** | | |
| | Included in Package | 1 - 10m Active DisplayPort Cable - M/M |
| | Package Width | 13.0 in [33 cm] |
| | Package Depth | 10.0 in [25.5 cm] |
| | Package Height | 1.6 in [40 mm] |
| | Shipping (Package) Weight | 16.4 oz [466 g] |
| **Connector(s)** | | |
| | Connector 1 (Quantity) | 1 |
| | Connector 1 | DisplayPort |
| | Connector 2 (Quantity) | 1 |
| | Connector 2 | DisplayPort |

***Product appearance and specifications are subject to change without notice.***