

50ft (15m) Active DisplayPort Cable - 4K Ultra HD DisplayPort Cable - Long DP to DP Cable for Projector/Monitor - DP Video/Display Cord - Latching DP Connectors

**Product ID:** DISPL15MA



The DISPL15MA 15m Active DisplayPort Cable features a built-in active signal booster for a connection distance of up to 50 feet (15m) between your DisplayPort-enabled devices - more than double the DisplayPort connection distance limitation of 16ft, with no signal loss.

This durable yet lightweight active DP cable features a thinner 32 AWG wire construction that allows for a more flexible installation with minimal clutter. Plus, the cable features built-in amplifier circuitry which actively boosts the DisplayPort signal with no external power needed.

The 15m cable offers a bandwidth of 10.8 Gbps with support for maximum resolutions up to 4K x 2K 30Hz and optional audio support. The cable is both HDCP and DPCP capable, which ensures that digitally protected content is displayed properly.

This 15-meter Active DisplayPort cable is backed by StarTech.com's 2-year Warranty.

Please Note: This cable features unidirectional architecture which requires that the cable is installed in the correct direction. Please refer to the "source" and "display" labels on the DisplayPort connectors, in order to ensure that the display device (monitor, projector etc.) and the DisplayPort source are connected properly.

## Certifications, Reports and Compatibility



## Applications

- Connecting a DisplayPort display to a PC or alternative DisplayPort source, over long distances, with no signal loss

## Features

- **ACTIVE DISPLAYPORT CABLE:** Active 15m DisplayPort cable supports 4K (3840 x 2160p at 30Hz), 10.8 Gbps bandwidth, HBR, 8Ch Audio, Multi-Stream Transport (MST), GTC for precise audio channel timing & 3D Stereo (1080p at 60Hz)
- **ACTIVE CIRCUITRY:** Active bus powered amplifier boosts video signals over longer distances up to 15 m (no external power supply needed), supports additional color spaces
- **LIGHT AND DURABLE CABLE:** Long-lasting light-weight cable; 32AWG wire; Flexible PVC jacket; Superior EMI shielding with Al-Mylar foil and copper braid provides higher quality video and audio; Backwards compatible with DP 1.1
- **APPLICATIONS:** Ideal for home/offices/boardrooms/conference rooms/classrooms, works with your laptop/professional workstations with FirePro S9000/7000, W8100/7100/5100 or R5000 graphic cards; Use with UHD/4K monitors, projector or large display
- **SPECS:** 15 meter (50 foot) Black DisplayPort v1.1 Latching Male to Male 32 AWG PVC cable jacket Shield: Al-Mylar foil with Braid Protocols: HBR, MST, GTC 2-Year Warranty Note: DP connector labelled "Display" connects to the display side

---

### Hardware

Warranty	2 Years
Number of Conductors	19
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG

---

### Connector(s)

Connector A	1 - DisplayPort (20 pin)
Connector B	1 - DisplayPort (20 pin)

---

### Environmental

Operating Temperature	0C to 45C (32F to 113F)
Storage Temperature	-20C to 70C (-4F to 158F)

---

### Physical Characteristics

Color	Black
-------	-------

Connector Style	Straight
Wire Gauge	32 AWG
Cable Length	49.2 ft [15 m]
Product Length	49.2 ft [15.0 m]
Product Width	0.8 in [2.0 cm]
Product Height	0.6 in [1.4 cm]
Weight of Product	1.4 lb [0.6 kg]

---

#### Packaging Information

Package Quantity	1
Package Length	10.4 in [26.5 cm]
Package Width	10.6 in [27.0 cm]
Package Height	1.9 in [4.7 cm]
Shipping (Package) Weight	1.5 lb [0.7 kg]

---

#### What's in the Box

Included in Package	1 - 15m Active DisplayPort Cable - M/M
---------------------	--

---

***\*Product appearance and specifications are subject to change without notice.***