

DisplayPort 1.2 Cable with Latches - Certified, 3m

Product ID: DISPL3M



The DISPL3M 3m DisplayPort 1.2 Cable with latches provides a secure, connection between your DisplayPort-equipped devices and is capable of providing higher performance than either HDMI or dual link DVI.

The DP cable supports high resolutions of up to 4k x 2k (4096 x 2160) @ 60Hz with a maximum HBR2 bandwidth of 21.6 Gbps. The cable also supports Multi-Stream (MST) for daisy chaining multiple monitors and provides optional audio support.

The DISPL3M is backed by StarTech.com's Lifetime Warranty, for guaranteed reliability and ensures that digitally protected content is displayed properly, with both HDCP and DPCP capability.

Certifications, Reports and Compatibility

Applications

- Connecting a DisplayPort Display to a PC or other DisplayPort Source

Features

- High-resolution support of up to 4k x 2k
- Support for High Bit Rate 2 (HBR2) bandwidth of up to 21.6 Gbps
- Backward compatible with DisplayPort 1.1
- Designed and manufactured to DisplayPort 1.2 standards
- Supports the DPCP (DisplayPort Content Protection) standard in addition to HDCP

- Molded latching connectors with strain relief

Hardware

Warranty	Lifetime
Number of Conductors	19
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)

Connector(s)

Connector A	DisplayPort (20 pin)
Connector B	DisplayPort (20 pin)

Physical Characteristics

Color	Black
Connector Style	Latching
Wire Gauge	28 AWG
Cable Length	9.8 ft [3 m]
Cable OD	0.3 in [7.3 mm]
Product Length	9.8 ft [3.0 m]
Product Width	0.8 in [20.5 mm]
Product Height	0.4 in [10.8 mm]
Weight of Product	7.3 oz [207.0 g]

Packaging Information

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]



Package Height 0.9 in [22.0 mm]

Shipping (Package) Weight 7.5 oz [212.0 g]

What's in the Box

Included in Package 3m DisplayPort Cable 1.2 with Latches - M/M

****Product appearance and specifications are subject to change without notice.***

