

5m (15ft) DisplayPort 1.2 Cable - 4K x 2K Ultra HD VESA Certified DisplayPort Cable - DP to DP Cable for Monitor - DP Video/Display Cord - Latching DP Connectors

Product ID: DISPL5M



The DISPL5M DisplayPort 1.2 Cable with latches provides a secure connection between your DisplayPort-equipped devices and allows for a connection distance of up to 5-meters between your source and display.

The DP cable is capable of providing higher performance than either HDMI or dual link DVI with support for high resolutions of up to 4k x 2k (4096 x 2160) @ 60Hz and a maximum HBR2 bandwidth of 21.6 Gbps. The cable also supports Multi-Stream (MST) for daisy chaining multiple monitors and provides optional audio support.

The DISPL5M long DisplayPort cable is backed by StarTech.com's Lifetime Warranty, for guaranteed reliability and ensures that digitally protected content is displayed properly, with both HDCP and DPCP capability.

Certifications, Reports and Compatibility



Applications

- Connecting a DisplayPort Display to a PC or other DisplayPort Source

Features

- **HIGH PERFORMANCE CABLE:** This 5m (15ft) VESA Certified DisplayPort v1.2 cable supports 4K x 2K (3840x2400p 60Hz), 21.6 Gbps bandwidth, HBR2, 8Ch Audio, Multi-Stream Transport (MST), GTC for precise audio channel timing & 3D Stereo (2560x1600p 120Hz)

- **RELIABLE DESIGN:** Durable ABS connectors with flexible PVC strain relief & jacket prevents fraying/damage due to bending or rough usage; Metal connector sub-structure provides EMI shielding; Latching DP connectors prevent accidental disconnection
- **QUALITY CONSTRUCTION:** 26AWG wire with gold-plated connectors for improved signal integrity and reliability; Superior EMI shielding with Al-Mylar foil and copper braid provides higher quality video and audio; Backwards compatible with DP 1.1
- **APPLICATIONS:** Ideal for home/offices/boardrooms/conference rooms/classrooms; works with your professional workstations with FirePro S9000/7000, W8100/7100/5100 or R5000 graphic cards; Use with 1080p/UHD/4K monitors, projector or large display
- **SPECS:** 5 m (15 ft) Black DisplayPort v1.2 DP Latching Male to Male 26/28 AWG PVC cable jacket, ABS connector shell Shield: Al-Mylar foil with Braid Protocols: HBR 2, MST, GTC

Hardware

Warranty	Lifetime
Number of Conductors	19
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)

Connector(s)

Connector A	1 - DisplayPort (20 pin)
Connector B	1 - DisplayPort (20 pin)

Physical Characteristics

Color	Black
Connector Style	Latching
Wire Gauge	26/28 AWG
Cable Length	16.4 ft [5 m]
Cable OD	0.3 in [7.3 mm]
Product Length	16.4 ft [5.0 m]
Product Width	0.8 in [2.0 cm]

Product Height	0.4 in [1.1 cm]
Weight of Product	13.2 oz [374.0 g]

Packaging Information

Package Quantity	1
Package Length	13.0 in [33.0 cm]
Package Width	9.9 in [25.2 cm]
Package Height	1.7 in [4.3 cm]
Shipping (Package) Weight	13.4 oz [379.0 g]

What's in the Box

Included in Package	1 - 5m Latching DisplayPort Cable
---------------------	-----------------------------------

**Product appearance and specifications are subject to change without notice.*