

7m DisplayPort Cable with Latches - M/M

Product ID: DISPL7M



The DISPL7M DisplayPort Cable with latches provides a secure connection between your DisplayPort-enabled devices and allows for a connection distance of up to 7 meters between your source and display.

With a bandwidth of 10.8Gbps and support for maximum resolutions up to 2560x1600 (WQXGA), as well as optional audio support, this 7-meter DisplayPort cable offers impressive video capability and ensures that digitally protected content is displayed properly, with both HDCP and DPCP capability.

The DISPL7M is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Connecting a DisplayPort display to a PC or other DisplayPort source

Features

- Molded latching connectors with strain relief
 - Designed and manufactured to DisplayPort standards
 - Supports the DPCP (DisplayPort Content Protection) standard in addition to HDCP
 - Offers 7m in cable length
-

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)

Connector(s)

Connector A	DisplayPort (20 pin)
Connector B	DisplayPort (20 pin)

Physical Characteristics

Color	Black
Connector Style	Latching
Wire Gauge	26 AWG (0.404 mm)
Cable Length	23.0 ft [7 m]
Product Length	23.0 ft [7.0 m]
Product Width	0.0 in [0.0 mm]
Product Height	0.0 in [0.0 mm]
Weight of Product	18.1 oz [513.0 g]

Packaging Information

Package Quantity	1
Package Length	13.0 in [33.0 cm]
Package Width	9.9 in [25.2 cm]
Package Height	2.1 in [53.0 mm]
Shipping (Package) Weight	18.5 oz [523.0 g]

What's in the Box



Included in Package 7m DisplayPort Cable with Latches - M/M

****Product appearance and specifications are subject to change without notice.***

