

10- Pack 15ft (4.6m) DisplayPort 1.2 Cable - 4K x 2K Ultra HD VESA Certified DisplayPort Cable - DP to DP Cable for Monitor - DP Video/Display Cord - Latching DP Connectors

**Product ID:** DISPLPORT15L10PK



This DisplayPort cable multipack provides reliable long-distance connections between your sources and displays. The 10 pack DP cables support resolutions up to 4k x 2k (4096 x 2160) @ 60Hz for high quality video.

The male to male DisplayPort cables support DP 1.2 features, including a maximum HBR2 bandwidth of 21.6 Gbps. The DP cables also support Multi-Stream (MST) for daisy-chaining multiple monitors with optional audio support. And they are backwards compatible with DisplayPort 1.1.

The black DP cables feature latches on each connector that provide a secure connection between your devices. They have a professional grade 28 AWG construction allowing for flexible and clean quality installations.

The DisplayPort cable bulk pack provides a convenient solution for businesses in need of multiple cables. Providing high quality and reliable DP connections for all business needs.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to our customers. Our local StarTech.com Technical Advisors have a broad product expertise and work directly with StarTech.com Engineers to provide support for our customers both pre and post-sales.

## Certifications, Reports and Compatibility



## Applications

- Connecting a DisplayPort Display to a PC or other DisplayPort Source

## Features

- **HIGH PERFORMANCE CABLE:** This 15ft (4.6m) VESA Certified DisplayPort v1.2 cable supports 4K x 2K (3840x2400p 60Hz), 21.6 Gbps bandwidth, HBR2, 8Ch Audio, Multi-Stream Transport (MST), GTC for precise audio channel timing & 3D Stereo (2560x1600p 120Hz)
- **RELIABLE DESIGN:** Durable ABS connectors with flexible PVC strain relief & jacket prevents fraying/damage due to bending or rough usage; Metal connector sub-structure provides EMI shielding; Latching DP connectors prevent accidental disconnection
- **QUALITY CONSTRUCTION:** 28AWG wire with gold-plated connectors for improved signal integrity and reliability; Superior EMI shielding with Al-Mylar foil and copper braid provides higher quality video and audio; Backwards compatible with DP 1.1
- **APPLICATIONS:** Ideal for home/offices/boardrooms/conference rooms/classrooms; works with your professional workstations with FirePro S9000/7000, W8100/7100/5100 or R5000 graphic cards; Use with 1080p/UHD/4K monitors, projector or large display
- **SPECS:** 15 ft (4,6 m) Black DisplayPort v1.2 DP Latching Male to Male 26/28 AWG PVC cable jacket, ABS connector shell Shield: Al-Mylar foil with Braid Protocols: HBR 2, MST, GTC

---

### Hardware

Warranty	Lifetime
Number of Conductors	19
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG

---

### Connector(s)

Connector A	1 - DisplayPort (20 pin)
Connector B	1 - DisplayPort (20 pin)

---

### Physical Characteristics

Color	Black
Connector Style	Latching
Wire Gauge	28 AWG

Cable Length	15.0 ft [4.6 m]
Product Length	15.0 ft [4.6 m]
Product Width	0.8 in [2.0 cm]
Product Height	0.5 in [1.3 cm]
Weight of Product	12.5 oz [354.0 g]

---

#### Packaging Information

Package Quantity	10
Package Length	12.6 in [32.0 cm]
Package Width	9.4 in [24.0 cm]
Package Height	8.9 in [22.5 cm]
Shipping (Package) Weight	8.8 lb [4.0 kg]

---

#### What's in the Box

Included in Package	10 - DisplayPort Cable
---------------------	------------------------

---

#### Warranty Information

Warranty	Lifetime
----------	----------

---

***\*Product appearance and specifications are subject to change without notice.***