

15 ft. (4.6 m) DisplayPort Cable with Latches - 10-Pack

Product ID: DISPLPORT15L10PK



This DisplayPort cable multipack provides reliable long-distance connections between your sources and displays. The 10 pack DP cables support resolutions up to 4k x 2k (4096 x 2160) @ 60Hz for high quality video.

The male to male DisplayPort cables support DP 1.2 features, including a maximum HBR2 bandwidth of 21.6 Gbps. The DP cables also support Multi-Stream (MST) for daisy-chaining multiple monitors with optional audio support. And they are backwards compatible with DisplayPort 1.1.

The black DP cables feature latches on each connector that provide a secure connection between your devices. They have a professional grade 28 AWG construction allowing for flexible and clean quality installations.

The DisplayPort cable bulk pack provides a convenient solution for businesses in need of multiple cables. Providing high quality and reliable DP connections for all business needs.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to our customers. Our local StarTech.com Technical Advisors have a broad product expertise and work directly with StarTech.com Engineers to provide support for our customers both pre and post-sales.

DISPLPORT15L10PK is backed by StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connecting a DisplayPort Display to a PC or other DisplayPort Source

Features

- Experience high resolution DisplayPort video with resolutions of up to 4K x 2K
- Supports High Bit Rate 2 (HBR2) bandwidth of up to 21.6 Gbps
- Provides molded latching strain relief connectors
- Ideal solution for business in need of a DisplayPort cable multipack

Hardware

| | |
|-----------------------|--------------------------------|
| Warranty | Lifetime |
| Number of Conductors | 19 |
| Connector Plating | Nickel |
| Cable Jacket Material | PVC - Polyvinyl Chloride |
| Cable Shield Material | Aluminum-Mylar Foil with Braid |
| Fire Rating | CMG Rated (General Purpose) |

Connector(s)

| | |
|-------------|--------------------------|
| Connector A | 1 - DisplayPort (20 pin) |
| Connector B | 1 - DisplayPort (20 pin) |

Physical Characteristics

| | |
|-------------------|-------------------|
| Color | Black |
| Connector Style | Latching |
| Wire Gauge | 28 AWG |
| Cable Length | 15.0 ft [4.6 m] |
| Product Length | 15.0 ft [4.6 m] |
| Product Width | 0.8 in [2.0 cm] |
| Product Height | 0.5 in [1.3 cm] |
| Weight of Product | 12.5 oz [354.0 g] |

**Packaging
Information**

| | |
|------------------------------|-------------------|
| Package Quantity | 10 |
| Package Length | 12.6 in [32.0 cm] |
| Package Width | 9.4 in [24.0 cm] |
| Package Height | 8.9 in [22.5 cm] |
| Shipping (Package) Weight | 8.8 lb [4.0 kg] |

What's in the Box

| | |
|---------------------|------------------------|
| Included in Package | 10 - DisplayPort Cable |
|---------------------|------------------------|

****Product appearance and specifications are subject to change without notice.***