

20ft (6m) DisplayPort Cable - 2560 x 1440p - DisplayPort to DisplayPort Cable - DP to DP Cable for Monitor - DP Video/Display Cord - Latching DP Connectors - HDCP & DPCP

Produkt-ID: DISPLPORT20L



The DISPLPORT20L 20-foot DisplayPort® Cable supports a maximum bandwidth of 10.8 Gbps, and is capable of providing higher performance than either HDMI® or dual link DVI, while supporting next generation multimedia applications with a maximum resolution capability of up to WQXGA (2560×1600).

The cable features latching connectors, with support for two-way display connectivity and optional audio support.

Featuring 26 gauge (AWG) pure copper wire, the cable includes Aluminum and Mylar shielding to help eliminate EMI and RFI interference and maintain signal integrity without any degradation of quality.

This 20-foot DisplayPort cable is both HDCP and DPCP capable, ensuring that digitally protected content is displayed properly on the connected display.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Anschließen eines DisplayPort®-Displays an einen PC oder eine andere DisplayPort-Quelle

Merkmale

- **HIGH PERFORMANCE CABLE:** This 20ft (6m) DisplayPort to DisplayPort cable supports 2K (2560x1440p) 30Hz, Full HD (1920x1200p) 60Hz, 10.8 Gbps bandwidth, Multi-Stream Transport (MST), 5.1, 7.1 Audio Channel, GTC for precise audio channel timing & 3D Stereo
- Entwickelt und gefertigt nach DisplayPort®-Normen
- Unterstützt die Norm DPCP (DisplayPort Content Protection, DisplayPort-Inhaltsschutz) und HDCP
- **APPLICATIONS:** Ideal for home/offices/boardrooms/conference rooms/classrooms; works with your professional workstations with FirePro™ S9000/7000, W8100/7100/5100 or R5000 graphic cards; Use with 1080p/UHD/4K monitors, projector or large display
- **SPECS:** 20 ft (6 m) | Black | DisplayPort v1.0 | DP Latching Male to Male | 26 AWG | PVC cable jacket, ABS connector shell | Shield: Al-Mylar foil with Braid | Protocols: MST, GTC | Lifetime Warranty

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	19
Steckverbinderplatten	Nickel
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Typ der Kabelabschirmung	Aluminium-Mylar-Folie mit Geflecht
Feuerwiderstandssklasse	Ausgelegt gemäß CMG (Mehrzweck)
e	

Steckverbinder

Steckverbinder A	1 - DisplayPort (20-polig)
Steckverbinder B	1 - DisplayPort (20-polig)

Physische Eigenschaften

Farbe	Schwarz
Steckverbinderart	Einrastend
Drahtstärke	26 AWG (0.404 mm)
Kabellänge	20.0 ft [6.1 m]

Außendurchmesser des Kabels	0.3 in [8.5 mm]
Produktlänge	20.0 ft [6.1 m]
Produktbreite	0.8 in [2.0 cm]
Produkthöhe	0.4 in [1.1 cm]
Produktgewicht	15.9 oz [450.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	7.4 in [18.7 cm]
Paketbreite	9.8 in [25.0 cm]
Pakethöhe	1.6 in [4.1 cm]
Versandgewicht (Verpackung)	1.0 lb [0.5 kg]

Verpackungsinhalt

Im Paket enthalten	1 - 20 ft DisplayPort® Cable with Latches - M/M
--------------------	---

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.