

25ft (7.5m) DisplayPort Cable - 2560 x 1440p - DisplayPort to DisplayPort Cable - DP to DP Cable for Monitor - DP Video/Display Cord - Latching DP Connectors - HDCP & DPCP

Produkt-ID: DISPLPORT25L



The DISPLPORT25L 25-foot DisplayPort® cable provides a connection of up to 25ft between a DisplayPort source and a DisplayPort display, with no loss of signal quality – almost/more than double the typical DisplayPort connection distance limitation of 16ft. Its 26 gauge (AWG) pure copper wire, and Aluminum and Mylar shielding helps to eliminate EMI and RFI interference. Delivering a maximum bandwidth of 10.8 Gbps, the DISPLPORT25L is capable of providing higher performance than either HDMI® or dual link DVI and supporting next generation multimedia applications with a maximum resolution capability of up to WQXGA (2560×1600).

The DisplayPort cable's small, USB-sized latching connectors support two-way display connectivity and optional audio support.

The DISPLPORT25L DisplayPort cable is both HDCP and DPCP capable, ensuring that digitally protected content is displayed properly on the connected display.

## Zertifikate Berichte und Kompatibilität



## Anwendungen

- Connecting a DisplayPort® display to a PC or alternative DisplayPort source

## Merkmale

- **HIGH PERFORMANCE CABLE:** This 25ft (7m) DisplayPort to DisplayPort cable supports 2K (2560x1440p) 30Hz, Full HD (1920x1200p) 60Hz, 10.8 Gbps bandwidth, Multi-Stream Transport (MST), 5.1, 7.1 Audio Channel, GTC for precise audio channel timing & 3D Stereo
- **RELIABLE DESIGN:** Durable ABS connectors with flexible PVC strain relief & jacket prevents fraying/damage due to bending or rough usage; Metal connector sub-structure provides EMI shielding; Latching DP connectors prevent accidental disconnection
- **QUALITY CONSTRUCTION:** 26AWG wire with gold-plated connectors for improved signal integrity and reliability; Superior EMI shielding with Al-Mylar foil and copper braid provides higher quality video and audio; Backwards compatible with DP 1.1
- **APPLICATIONS:** Ideal for home/offices/boardrooms/conference rooms/classrooms; works with your professional workstations with FirePro™ S9000/7000, W8100/7100/5100 or R5000 graphic cards; Use with 1080p/UHD/4K monitors, projector or large display
- **SPECS:** 25 ft (7 m) | Black | DisplayPort v1.0 | DP Latching Male to Male | 26 AWG | PVC cable jacket, ABS connector shell | Shield: Al-Mylar foil with Braid | Protocols: MST, GTC | Lifetime Warranty

### Hardware

|                          |                                    |
|--------------------------|------------------------------------|
| Garantiebestimmungen     | Lifetime                           |
| Anzahl von Leitern       | 19                                 |
| Steckverbinderplatten    | Nickel                             |
| Typ der Kabelummantelung | PVC - Polyvinyl Chloride           |
| Typ der Kabelabschirmung | Aluminium-Mylar-Folie mit Geflecht |
| Feuerwiderstandsklasse   | Ausgelegt gemäß CMG (Mehrzweck)    |

### Steckverbinder

|                  |                            |
|------------------|----------------------------|
| Steckverbinder A | 1 - DisplayPort (20-polig) |
| Steckverbinder B | 1 - DisplayPort (20-polig) |

### Physische Eigenschaften

|                   |            |
|-------------------|------------|
| Farbe             | Schwarz    |
| Steckverbinderart | Einrastend |

|                             |                   |
|-----------------------------|-------------------|
| Drahtstärke                 | 26 AWG (0.404 mm) |
| Kabellänge                  | 25.0 ft [7.6 m]   |
| Außendurchmesser des Kabels | 0.3 in [8.5 mm]   |
| Produktlänge                | 25.0 ft [7.6 m]   |
| Produktbreite               | 0.8 in [2.1 cm]   |
| Produkthöhe                 | 0.6 in [1.5 cm]   |
| Produktgewicht              | 1.3 lb [0.6 kg]   |

---

#### Verpackungsinformationen

|                             |                   |
|-----------------------------|-------------------|
| Paketmenge                  | 1                 |
| Paketlänge                  | 8.3 in [21.0 cm]  |
| Paketbreite                 | 12.8 in [32.5 cm] |
| Pakethöhe                   | 1.7 in [4.3 cm]   |
| Versandgewicht (Verpackung) | 1.3 lb [0.6 kg]   |

---

#### Verpackungsinhalt

|                    |                                                 |
|--------------------|-------------------------------------------------|
| Im Paket enthalten | 1 - 25 ft DisplayPort® Cable with Latches - M/M |
|--------------------|-------------------------------------------------|

---

#### Garantieinformationen

|          |          |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|

---

\* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.