

3ft (91cm) DisplayPort 1.2 Cable - 4K x 2K Ultra HD VESA Certified DisplayPort Cable - DP to DP Cable for Monitor - DP Video/Display Cord - Latching DP Connectors

Produkt-ID: DISPLPORT3L



The DISPLPORT3L 3ft DisplayPort™ 1.2 Cable with latches provides a secure, connection between your DisplayPort-equipped devices and is capable of providing higher performance than either HDMI® or dual link DVI.

The DP cable supports high resolutions of up to 4k x 2k (4096 x 2160) @ 60Hz with a maximum HBR2 bandwidth of 21.6 Gbps. The cable also supports Multi-Stream (MST) for daisy chaining multiple monitors and provides optional audio support.

The DISPLPORT3L is backed by StarTech.com's Lifetime Warranty, for guaranteed reliability and ensures that digitally protected content is displayed properly, with both HDCP and DPCP capability.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Anschließen eines DisplayPort-Displays an einen PC oder eine andere DisplayPort-Quelle

Merkmale

- HIGH PERFORMANCE CABLE: This 3ft (1m) VESA Certified DisplayPort v1.2 cable supports 4K x 2K

(3840x2400p 60Hz), 21.6 Gbps bandwidth, HBR2, 8Ch Audio, Multi-Stream Transport (MST), GTC for precise audio channel timing & 3D Stereo (2560x1600p 120Hz)

- **RELIABLE DESIGN:** Durable ABS connectors with flexible PVC strain relief & jacket prevents fraying/damage due to bending or rough usage; Metal connector sub-structure provides EMI shielding; Latching DP connectors prevent accidental disconnection
- **QUALITY CONSTRUCTION:** 28AWG wire with gold-plated connectors for improved signal integrity and reliability; Superior EMI shielding with Al-Mylar foil and copper braid provides higher quality video and audio; Backwards compatible with DP 1.1
- Entwickelt und gefertigt nach DisplayPort-Normen
- Unterstützt die Norm DPCP (DisplayPort Content Protection, DisplayPort-Inhaltsschutz) und HDCP

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	19
Steckverbinderplatten	Nickel
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Typ der Kabelabschirmung	Aluminium-Mylar-Folie mit Geflecht
Feuerwiderstandsklasse	Ausgelegt gemäß CMG (Mehrzweck)

Leistung

Max. Digitalauflösungen	4k x 2k (4096 x 2160) @ 60Hz
-------------------------	------------------------------

Steckverbinder

Steckverbinder A	1 - DisplayPort (20-polig)
Steckverbinder B	1 - DisplayPort (20-polig)

Physische Eigenschaften

Farbe	Schwarz
Steckverbinderart	Einrastend
Drahtstärke	28 AWG

Kabellänge	3.0 ft [0.9 m]
Außendurchmesser des Kabels	0.3 in [6.5 mm]
Produktlänge	37.0 in [94.0 cm]
Produktbreite	0.8 in [2.0 cm]
Produkthöhe	0.6 in [1.5 cm]
Produktgewicht	2.8 oz [79.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	5.2 in [13.1 cm]
Paketbreite	13.9 in [35.2 cm]
Pakethöhe	1.3 in [3.3 cm]
Versandgewicht (Verpackung)	2.8 oz [80.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - 3 ft DisplayPort™ Cable with Latches - M/M
--------------------	--

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.