

91 cm DisplayPort 1.2 kabel met vergrendeling M/M - DisplayPort 4k

Product ID: DISPLPORT3L



The DISPLPORT3L3ft DisplayPort 1.2 Cable with latches provides a secure, connection between your DisplayPort-equipped devices and is capable of providing higher performance than either HDMI or dual link DVI.

The DP cable supports high resolutions of up to 4k x 2k (4096 x 2160) @ 60Hz with a maximum HBR2 bandwidth of 21.6 Gbps. The cable also supports Multi-Stream (MST) for daisy chaining multiple monitors and provides optional audio support.

The DISPLPORT3L is backed by StarTech.com's Lifetime Warranty, for guaranteed reliability and ensures that digitally protected content is displayed properly, with both HDCP and DPCP capability.

Certifications, Reports and Compatibility



Applications

- Connecting a DisplayPort Display to a PC or other DisplayPort Source

Features

- **UPGRADED VERSION NOW AVAILABLE:** DP14MM1M supports DisplayPort 1.4, 8K 60Hz (7680x4320), 4K 120Hz (3840x2160), VESA Certified; 32.4Gbps bandwidth; HDR, HBR3, 32ch audio, FEC error control
- **SECURE DESIGN:** The DisplayPort 1.2 Cable with latches provides a secure, connection between your DP-equipped devices and is capable of providing higher performance than either HDMI or dual link DVI
- **ULTIMATE PERFORMANCE:** The DP cable supports high resolutions of up to 4k x 2k (4096 x 2160) @ 60Hz with a maximum HBR2 bandwidth of 21.6 Gbps; HDCP and DPCP capable
- **EXTENSIVE CAPABILITIES:** The DisplayPort 1.2 cable supports Multi-Stream (MST) for daisy chaining multiple

monitors and provides optional audio support

- THE STARTECH.COM ADVANTAGE: StarTech.com offers a lifetime warranty and free lifetime technical support on this 3 ft cable and has been the choice of IT professionals and businesses since 1995
- Molded latching connectors with strain relief

Hardware	Warranty	Lifetime
	Aantal geleiders	19
	Connectormateriaal	Nickel
	Type kabelmantel	PVC - Polyvinyl Chloride
	Kabelafscherming	Aluminum-Mylar Foil with Braid
	Brandbestendigheid	CMG Rated (General Purpose)
Prestaties	Maximale digitale resoluties	4k x 2k (4096 x 2160) @ 60Hz
Connector(en)	Connector A	DisplayPort (20 pin)
	Connector B	DisplayPort (20 pin)
Fysieke eigenschappen	Kleur	Black
	Stijl connector	Latching
	Draaddikte	28 AWG
	Kabellengte	36.0 in [9.1 cm]
	Buitendiameter kabel	0.3 in [6.5 mm]
	Lengte product	37.0 in [9.4 cm]
	Breedte product	0.8 in [20.000 mm]
	Hoogte product	0.6 in [15.000 mm]
Gewicht product	2.8 oz [79.000 g]	
Verpakkingsinformatie	Verpakkingsaantal	1
	Package Length	8.7 in [2.2 cm]
	Package Width	7.9 in [2.0 cm]
	Package Height	0.8 in [20.000 mm]
	Verzendgewicht (verpakt)	3.1 oz [88.000 g]
Wat wordt er meegeleverd	Meegeleverd	3 ft DisplayPort Cable with Latches - M/M

****Product appearance and specifications are subject to change without notice.***

