

3 ft DisplayPort 1.2 Cable with Latches M/M – DisplayPort 4k

**Product ID:** DISPLPORT3L



The DISPLPORT3L 3ft DisplayPort 1.2 Cable with latches provides a secure, connection between your DisplayPort-equipped devices and is capable of providing higher performance than either HDMI or dual link DVI.

The DP cable supports high resolutions of up to 4k x 2k (4096 x 2160) @ 60Hz with a maximum HBR2 bandwidth of 21.6 Gbps. The cable also supports Multi-Stream (MST) for daisy chaining multiple monitors and provides optional audio support.

The DISPLPORT3L is backed by StarTech.com's Lifetime Warranty, for guaranteed reliability and ensures that digitally protected content is displayed properly, with both HDCP and DPCP capability.

## Certifications, Reports and Compatibility

### Applications

- Connecting a DisplayPort Display to a PC or other DisplayPort Source

### Features

- **UPGRADED VERSION NOW AVAILABLE:** DP14MM1M supports DisplayPort 1.4, 8K 60Hz (7680x4320), 4K 120Hz (3840x2160), VESA Certified; 32.4Gbps bandwidth; HDR, HBR3, 32ch audio, FEC error control
- **SECURE DESIGN:** The DisplayPort 1.2 Cable with latches provides a secure, connection between your DP-equipped devices and is capable of providing higher performance than either HDMI or dual link DVI
- **ULTIMATE PERFORMANCE:** The DP cable supports high resolutions of up to 4k x 2k (4096 x 2160) @ 60Hz with a maximum HBR2 bandwidth of 21.6 Gbps; HDCP and DPCP capable

- **EXTENSIVE CAPABILITIES:** The DisplayPort 1.2 cable supports Multi-Stream (MST) for daisy chaining multiple monitors and provides optional audio support
- **THE STARTECH.COM ADVANTAGE:** StarTech.com offers a lifetime warranty and free lifetime technical support on this 3 ft cable and has been the choice of IT professionals and businesses since 1995

---

### Prominence

Warranty	Lifetime
Description CDW 75 - 1st Line	StarTech.com 3ft VESA Certified DisplayPort 1.2 Cable w/ Latches DP 4K 60Hz

---

### Hardware

Number of Conductors	19
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)

---

### Performance

Maximum Digital Resolutions	4k x 2k (4096 x 2160) @ 60Hz
-----------------------------	------------------------------

---

### Connector(s)

Connector A	DisplayPort (20 pin)
Connector B	DisplayPort (20 pin)

---

### Physical Characteristics

Color	Black
Connector Style	Latching
Wire Gauge	28 AWG
Cable Length	36.0 in [91.4 cm]
Cable OD	0.3 in [6.5 mm]
Product Length	37.0 in [94.0 cm]
Product Width	0.8 in [20.0 mm]



Product Height	0.6 in [15.0 mm]
Weight of Product	2.8 oz [79.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.8 in [20.0 mm]
Shipping (Package) Weight	3.1 oz [88.0 g]

---

**What's in the Box**

Included in Package	3 ft DisplayPort Cable with Latches - M/M
---------------------	---

---

***\*Product appearance and specifications are subject to change without notice.***

