

6ft (1.8m) DisplayPort 1.2 Cable 10 Pack, 4K x 2K Ultra HD VESA Certified DisplayPort Cable, HBR2, DP to DP Cable for Monitor, Latching DP Connectors - DP 1.2 Cable Male/Male

Produkt-ID: DISPLPORT6L10PK



This DisplayPort cable provides a secure connection between your DisplayPort equipped devices and is capable of providing higher performance than either HDMI® or dual-link DVI.

The DP cable supports high resolutions of up to 4K x 2K (4096 x 2160, 60Hz) with a maximum HBR2 bandwidth of 21.6Gbps, as well as optional audio support. The cable also supports Multi-Stream Transport (MST) for daisy chaining multiple monitors.

The 6-foot cable is DisplayPort (VESA) certified to support DP 1.2 specifications and ensure a high-quality, reliable connection for all of your DisplayPort devices.

The DISPLPORT6L is backed by a StarTech.com lifetime warranty for guaranteed reliability and ensures that digitally protected content is displayed properly, with both HDCP and DPCP capability.

Zertifikate Berichte und Kompatibilität



Anwendungen

Merkmale

- **HIGH PERFORMANCE CABLE:** This 10 pack 6ft (2m) VESA Certified DisplayPort v1.2 cable supports 4K x 2K (3840x2400p 60Hz), 21.6 Gbps bandwidth, HBR2, 8Ch Audio, Multi-Stream Transport (MST), GTC for precise audio channel timing & 3D Stereo (2560x1600p 120Hz)
- **RELIABLE DESIGN:** Durable ABS connectors with flexible PVC strain relief & jacket prevents fraying/damage due to bending or rough usage; Metal connector sub-structure provides EMI shielding; Latching DP connectors prevent accidental disconnection
- **QUALITY CONSTRUCTION:** 28AWG wire with gold-plated connectors for improved signal integrity and reliability; Superior EMI shielding with Al-Mylar foil and copper braid provides higher quality video and audio; Backwards compatible with DP 1.1
- **APPLICATIONS:** Ideal for home/offices/boardrooms/conference rooms/classrooms; works with your professional workstations with FirePro™ S9000/7000, W8100/7100/5100 or R5000 graphic cards; Use with 1080p/UHD/4K monitors, projector or large display
- **SPECS:** 6 ft (2 m) | Black | DisplayPort v1.2 | DP Latching Male to Male | 28 AWG | PVC cable jacket, ABS connector shell | Shield: Al-Mylar foil with Braid | Protocols: HBR 2, MST, GTC | Lifetime Warranty

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	19
Steckverbinderplatten	Gold
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Typ der Kabelabschirmung	Aluminium-Mylar-Folie mit Geflecht
Feuerwiderstandsklasse	Ausgelegt gemäß CMG (Mehrzweck)

Steckverbinder

Steckverbinder A	1 - DisplayPort (20-polig)
Steckverbinder B	1 - DisplayPort (20-polig)

Physische Eigenschaften

Farbe	Schwarz
Steckverbinderart	Einrastend

Drahtstärke	28 AWG
Kabellänge	6.0 ft [1.8 m]
Außendurchmesser des Kabels	0.3 in [7.3 mm]
Produktlänge	6.0 ft [1.8 m]
Produktbreite	0.8 in [2.1 cm]
Produkthöhe	0.5 in [1.3 cm]
Produktgewicht	4.3 oz [122.0 g]

Verpackungsinformationen

Paketmenge	10
Paketlänge	11.0 in [27.9 cm]
Paketbreite	12.8 in [32.6 cm]
Pakethöhe	4.3 in [10.8 cm]
Versandgewicht (Verpackung)	3.1 lb [1.4 kg]

Verpackungsinhalt

Im Paket enthalten	10 - 6 ft DisplayPort™ 1.2 Cable with Latches - M/M
--------------------	-----------------------------------------------------

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.