

DisplayPort 1.2 Cable with Latches - Certified, 6 ft

Product ID: DISPLPORT6L



This DisplayPort cable provides a secure connection between your DisplayPort equipped devices and is capable of providing higher performance than either HDMI or dual-link DVI.

The DP cable supports high resolutions of up to 4K x 2K (4096 x 2160, 60Hz) with a maximum HBR2 bandwidth of 21.6Gbps, as well as optional audio support. The cable also supports Multi-Stream Transport (MST) for daisy chaining multiple monitors.

The 6-foot cable is DisplayPort (VESA) certified to support DP 1.2 specifications and ensure a high-quality, reliable connection for all of your DisplayPort devices.

The DISPLPORT6L is backed by a StarTech.com lifetime warranty for guaranteed reliability and ensures that digitally protected content is displayed properly, with both HDCP and DPCP capability.

Certifications, Reports and Compatibility

Applications

- Connecting a DisplayPort display to a PC or other DisplayPort source

Features

- High-resolution support up to 4K x 2K
- Support for High Bit Rate 2 (HBR2) bandwidth of up to 21.6Gbps
- Backward compatible with DisplayPort 1.1

- Designed and manufactured to DisplayPort 1.2 standards
- Supports the DPCP (DisplayPort Content Protection) standard in addition to HDCP
- Molded latching connectors with strain relief
- DisplayPort (VESA) certified

Hardware

| | |
|-----------------------|--------------------------------|
| Warranty | Lifetime |
| Number of Conductors | 19 |
| Connector Plating | Nickel |
| Cable Jacket Material | PVC - Polyvinyl Chloride |
| Cable Shield Material | Aluminum-Mylar Foil with Braid |
| Fire Rating | CMG Rated (General Purpose) |

Connector(s)

| | |
|-------------|----------------------|
| Connector A | DisplayPort (20 pin) |
| Connector B | DisplayPort (20 pin) |

Physical Characteristics

| | |
|-------------------|------------------|
| Color | Black |
| Connector Style | Latching |
| Wire Gauge | 28 AWG |
| Cable Length | 6.0 ft [1.8 m] |
| Cable OD | 0.3 in [6.5 mm] |
| Product Length | 6.0 ft [1.8 m] |
| Product Width | 0.8 in [20.9 mm] |
| Product Height | 0.5 in [12.8 mm] |
| Weight of Product | 4.8 oz [135.0 g] |

Packaging Information



| | |
|---------------------------|------------------|
| Package Length | 8.7 in [22.0 cm] |
| Package Width | 7.9 in [20.0 cm] |
| Package Height | 1.2 in [30.0 mm] |
| Shipping (Package) Weight | 4.7 oz [132.0 g] |

What's in the Box

| | |
|---------------------|---|
| Included in Package | 6 ft DisplayPort 1.2 Cable with Latches - M/M |
|---------------------|---|

****Product appearance and specifications are subject to change without notice.***

